

Keysight Technologies

E1738A

Air Temperature/Pressure/Humidity Sensor

Data Sheet



The E1738A Air Sensor is used with the Agilent E1736A USB Sensor Hub as part of the 5530 Laser Calibration System. The E1738A Air Sensor connects to the E1736A USB Sensor Hub via a detachable E1739A/B/C/D sensor cable. Sensor cables come in different lengths (5 m, 10 m, 15 m, 25 m), they have easy snap-on connectors so users can quickly change cable lengths as needed.

The E1738A Air Sensor monitors the air in the environment of the measurement to enable the laser calibration system to automatically adjust for the changes to the laser wavelength. The sensor has a magnetic base for ease of attachment.


Specifications			
E1738A Performance	Range	Resolution	Accuracy **
Air temperature	0 – 40°C (32 – 104°F)	0.004 °C (0.007 °F)	±0.1 °C (±0.2 °F)
Air pressure	70 – 110 kPa (10.2 – 16.0 psia)	5 Pa (0.001 psi)	±80 Pa (±0.012 psi)
Air humidity	10 – 90%	1%	±5%
** with yearly calibration			
Time constant	5 min typical		
Refresh rate	per 4 s (per 15 s with Metrology Application Software 10747F Rev F.04.04 or later)		
Power requirement	+3.3 V at maximum current (6 mA) +3.3 V at average current (0.6 mA)		
Power dissipation	2 mW typical		
Dimensions	Φ42 x 26 mm (Φ1.65 x 1.02 in)		
Weight	60 g (0.13 lb)		
Certification	ISO 17025		
Warranty	3 years (5 years option available)		

Related Literature

Publication title	Publication number
<i>Keysight 5530 Laser Calibration System Brochure</i>	5989-9354EN
<i>Keysight 5530 Laser Calibration System Data Sheet</i>	5989-9712EN

From Hewlett-Packard through Agilent to Keysight

For more than 75 years, we've been helping you unlock measurement insights. Our unique combination of hardware, software and people can help you reach your next breakthrough. **Unlocking measurement insights since 1939.**



1939

THE FUTURE

- myKeysight**
 - www.keysight.com/find/mykeysight
 - A personalized view into the information most relevant to you.
- Keysight Infoline**
 - www.keysight.com/find/service
 - Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.
- Keysight Channel Partners**
 - www.keysight.com/find/channelpartners
 - Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/5530

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-02-10-16)



www.keysight.com/go/quality
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2015
 Quality Management System



This information is subject to change without notice.
 © Keysight Technologies. 2012 - 2016
 Published in USA, March 14, 2016
 5989-8456EN
www.keysight.com