



# Agilent U1063A Acqiris High-Speed cPCI Digitizers DC270 and DC265

## Configuration Guide

### Introduction

This document provides configuration information for the Agilent U1063A 8-bit cPCI high-speed digitizers, Acqiris DC270 and DC265.

Required selections	
Bandwidth and sample rate	<i>Instructions: Select the required bandwidth and sample rate. Both options provide dual-channel performance with interleave capability.</i>
U1063A-001	Quad-channel, 150 MHz, 500 MS/s, 2 MSamples, DC265
U1063A-002	Quad-channel, 250 MHz, 1 GS/s, 128 kSamples, DC270
Input connector types	<i>Instructions: Select the required connector type for the four input channels and external trigger. Five connectors are required per card.</i>
U1063A-BNC	BNC connectors
U1063A-SMA	SMA connectors



**Agilent Technologies**

Options	
Memory options	<i>Instructions: No memory options are available for the U1063A-001 configuration. The standard U1063A-002 module is supplied with 128 kSamples of acquisition memory. If required, two memory extension options are available.</i>
U1063A-M2M	2 MSample acquisition memory for U1063A-002
U1063A-M8M	8 MSample acquisition memory for U1063A-002
Battery backup	<i>Instructions: Battery backup allows the storage of acquired data in on-board memory for up to 120 h.</i>
U1063A-BB1	Battery back-up
Calibration certificate	<i>Instructions: If required, and calibration data along with calibration certificate can be provided.</i>
U1063A-UK6	Calibration certificate and cal data
Manuals	<i>Instructions: Available from Agilent.com, optional hardcopy paper manuals and CD-ROM software and drivers are also available.</i>
U1061A-0B1	User manual kit for Acqiris 8-bit digitizers
U1061A-0B2	Programmers reference manual
U1061A-0B3	Programmers guide
U1061A-0B4	Software and drivers CD

## System Information

For creation of an integrated Compact PCI system, including chassis, interface or single board computer, please refer to the U1056B product.



U1056B Data converter system

[www.agilent.com](http://www.agilent.com)

Product specifications and descriptions in this document subject to change without notice.

For more information on the Acqiris product line, sales or services, see our website at:

[www.agilent.com/find/acqiris](http://www.agilent.com/find/acqiris)

## Contacts

### Agilent Acqiris Product Information

**USA** (800) 829-4444  
**Asia-Pacific** 61 3 9210 2890  
**Europe** 41 (22) 884 32 90

### Additional Agilent Contact Information

#### Americas

Canada (877) 894-4414  
 Latin America 305 269 7500  
 United States (800) 829-4444

#### Asia Pacific

Australia 1 800 629 485  
 China 800 810 0189  
 Hong Kong 800 938 693  
 India 1 800 112 929  
 Japan 0120 (421) 345  
 Korea 080 769 0800  
 Malaysia 1 800 888 848  
 Singapore 1 800 375 8100  
 Taiwan 0800 047 866  
 Thailand 1 800 226 008

#### Europe and Middle East

Austria 1800 629 485  
 Belgium 32 (0) 2404 93 40  
 Denmark 45 70 13 15 15  
 Finland 358 (0) 10 855 2100  
 France 0825 010 700\*  
 \*0.125 €/minute  
 Germany 49 7031 464 6333  
 Ireland 1890 924 204  
 Israel 972-3-9288-504/544  
 Italy 39 02 92 60 8484  
 Netherlands 31 (0) 20 547 2111  
 Spain 34 (91) 631 3300  
 Sweden 0200-88 22 55  
 Switzerland 0800 80 53 53  
 United Kingdom 44 (0) 118 9276201

Other European Countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

© Agilent Technologies, Inc. 2008  
 Printed in USA, November 27, 2008  
 5989-9188EN



**Agilent Technologies**