

Keysight Technologies

Buy Any Keysight Big5 Bench Instrument, Get A Complimentary Handheld!

Empower your engineers with a handy, reliable tool for carrying out tests and measurements on the go – whenever, wherever.

PROMOTION START DATE: April 1, 2017

END DATE: September 30, 2017

PROMOTION CODE: 6.015

Availability:

- United States, Canada, Latin America, Asia Pacific and Japan

Promotion conditions:

- Customers must purchase a new Keysight Bench product (listed in the table).
- Must be purchased from an authorized Keysight channel partner.
- Purchases of premium used equipment are not eligible.
- Complimentary U1242C handheld DMM comes with a 3-year warranty, batteries and user guides in multiple languages.
- Options can be purchased separately with the qualifying bench purchase.
- Keysight Technologies reserves the right to modify or discontinue this offering during the promotional period.
- If qualifying equipment in the original order is returned for any reason, the complimentary U1242C handheld DMM must also be returned.

Be eligible to receive the Keysight U1242C Handheld DMM (worth USD\$300) at no cost when you buy any Keysight Big5 Bench equipment (includes select power supplies, waveform generators and more).



The complimentary U1242C is IP67 certified (water and dust resistant) with up to 400 hours of long battery life.

Qualifying Keysight products include:

Big5 Bench Product Families	Model and Description
Big5 Bench 1: Low-Profile Modular Power System (MPS) & DC Power Analyzer	N6700B/C Low-Profile MPS Mainframe, 400 W
	N6701A/C Low-Profile MPS Mainframe, 600 W
	N6702A/C Low-Profile MPS Mainframe, 1200 W
	N6705B/C DC Power Analyzer, 600 W
Big5 Bench 2: Programmable DC Power Supply	E36102/3/4/5/6A DC Power Supply, Single Output, 30 W - 40 W models
	E36311/2/3A DC Power Supply, Triple Output, 80 W - 160 W models
Big5 Bench 3: DAQ/Data Logger Switch Unit	34970A Data Acquisition/Switch Unit with GPIB & RS232
	34972A LXI Data Acquisition Switch Unit with LAN & USB
Big5 Bench 4: Trueform Waveform Generator	33611/2A Waveform Generator, 80 MHz, single & dual channel models
	33621/2A Waveform Generator, 120 MHz, single & dual channel models
Big5 Bench 5: B2900 Precision SMU/ Low-Noise Power Source/ Picoammeter/Electrometer	B2901/2A Precision SMU, 100 fA, single & dual channel models
	B2911/2A Precision SMU, single & dual channel models
	B2961/2A Low-Noise Power Source, 10 fA/100 nV resolution, single & dual channel models
	B2981/3A Femto/Picoammeter, 0.01 fA (Battery option on B2983A)
	B2985/7A Electrometer/High Resistance Meter, 0.01 fA (Battery option on B2987A)



Three-Year Warranty
www.keysight.com/find/ThreeYearWarranty

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans
www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

This information is subject to change without notice.

© Keysight Technologies, 2017
 Published in USA, June 2, 2017
 5992-2215EN

www.keysight.com



Unlocking Measurement Insights

Take advantage of this offer

- Contact your Keysight authorized partner for more information or to place an order:
www.keysight.com/find/distributor
- To claim your complimentary handheld DMM:
www.keysight.com/find/BIG5BenchClaim