

Keysight Technologies 909F Precision Coaxial Termination DC to 18 Ghz

Data Sheet



Specifications

Specifications describe the instruments' warranted performance over the +15° to +35° C temperature range.

Supplemental characteristics as denoted by "typical", "nominal", or "approximate" are provided as information useful in applying the instrument, but are non-warranted performance parameters.

Frequency Range	dc to 18 GHz
Impedance (nominal)	50 Ω
Connector	909F, APC-7 Option 012, type-N (m) Option 013, type-N (f)
Reflection Coefficient (max): 909F	dc to 5 GHz, 0.0025 (1.005 SWR) 5 to 6 GHz, 0.005 (1.01 SWR) 6 to 18 GHz, 0.07 (1.15 SWR)
Option 012	dc to 2 GHz, 0.0035 (1.007 SWR) 2 to 3 GHz, 0.005 (1.01 SWR) 3 to 6 GHz, 0.01 (1.02 SWR) 6 to 18 GHz, 0.07 (1.15 SWR)
Option 013	dc to 2 GHz, 0.0035 (1.007 SWR) 2 to 3 GHz, 0.005 (1.01 SWR) 3 to 6 GHz, 0.01 (1.02 SWR) 6 to 18 GHz, 0.07 (1.15 SWR)
Power Rating	500 mW avg.; 100 W peak, 10 μS/pulse
Weight	net-60g (2 oz); shipping-200 g (8 oz)

Environmental

Temperature	Operating: +15° to +35° C Non Operating: -55° to +75° C
Altitude	Operating: 15,000 ft Non Operating: 50,000 ft
Humidity	Cycling 5 days, +40° C @ 95% RH
Vibration	0.015", 5-55-5 Hz, 15 min., 3 axes
Shock	100 g, 1-2 ms, 3 times 3 planes
EMC	Radiation interference is within the requirements of MIL-STD-461, method RE02, VDE 0871, CISPR Publication 11.

Description


Keysight Technologies, Inc.'s 909F family of precision low reflection loads are intended for use as calibration standards.

Tantalum nitride on sapphire thin-film technology is used for exceptional long-term impedance stability. To ensure the best possible wear resistance characteristics, gold-plated beryllium copper has been used for the connector contacts.

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/mta

