

Keysight Technologies

909C Precision Coaxial Termination DC - 2 GHz

Data Sheet



Description

The 909C is a precision low reflection load intended for use as a calibration standard.

Tantalum nitride on sapphire thin film technology is used for exceptional long term impedance stability. To insure the best possible wear resistance characteristics, gold plated beryllium copper has been used for the connector contacts.

Specifications

Frequency range:

DC - 2 GHz (Standard)

DC - 200 MHz (Option 200)

Impedance: 50 Ω

Connector:

909C, APC-7

Option 909C-012, type N (m)

Option 909C-013, type N (f)

Reflection coefficient:

909C (standard, Option 200): 0.0025 (1.005 SWR)

Option 012: 0.005 (1.01 SWR)

Option 013: 0.005 (1.01 SWR)

Power rating: 500 mW avg;


100 W peak, 10 μ s/pulse

Weight: net- 60 g (2 oz); shipping- 200 g (8oz)

Length: 51 mm (2 in)

From Hewlett-Packard through Agilent to Keysight

For more than 75 years, we've been helping you unlock measurement insights. Our unique combination of hardware, software and people can help you reach your next breakthrough. **Unlocking measurement insights since 1939.**



1939 THE FUTURE

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-01-01-16)

myKeysight www.keysight.com/find/mykeysight
 A personalized view into the information most relevant to you.

Keysight Infoline www.keysight.com/find/service
 Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

DEKRA Certified ISO 9001:2008 www.keysight.com/go/quality
 Quality Management System
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2008
 Quality Management System

Keysight Channel Partners www.keysight.com/find/channelpartners
 Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.