

# Keysight 909E

## Precision Coaxial Termination

dc - 3 GHz, 75  $\Omega$

### Data Sheet



### Specifications

Frequency range	dc - 3 GHz (Option 909E-101 or Option 909E-011)
Impedance (nominal)	75 $\Omega$
Connector	909E and Option 909E-201 - type N (m) Option 909E-011 - type N (f)
Reflection coefficient (max)	909E standard and Option 909E-011 dc - 2 GHz, 0.005 (1.01 SWR) 2 - 3 GHz, 0.01 (1.02 SWR)
Power rating	500 mW average; 100 W peak, 10 $\mu$ S/pulse

### Environmental

Temperature	Operating: +15 to +35 $^{\circ}$ C Non operating: -55 to +75 $^{\circ}$ C
Altitude	Operating: 15,000 ft Non operating: 50,000 ft
Humidity	Cycling five days, +40 $^{\circ}$ C @ 95% RH
Vibration	0.015", 5-55-5 Hz, 15 min., 3 axes
Shock	200 g, 3 ms, three times each plane
EMC	Radiation interference is within the requirements of MIL-STD-461, method RE02, VDE0871, CISPR publication 11
Weight	net - 60 g (2 oz) shipping - 200 g (8 oz)
Length	51 mm (2 in)

### Features and description

A Keysight Technologies, Inc. 909E is a precision, low reflection, 75  $\Omega$  load intended for use as a calibration standard. Tantalum nitride on sapphire thin film technology is used for exceptional long-term impedance stability. To insure the best possible wear resistance characteristics, gold plated beryllium copper has been used for the connector contacts.

myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)  
A personalized view into the information most relevant to you.



[www.axiestandard.org](http://www.axiestandard.org)  
AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



[www.lxistandard.org](http://www.lxistandard.org)  
LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



[www.pxisa.org](http://www.pxisa.org)  
PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



**Three-Year Warranty**  
[www.keysight.com/find/ThreeYearWarranty](http://www.keysight.com/find/ThreeYearWarranty)  
Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



**Keysight Assurance Plans**  
[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)  
Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



[www.keysight.com/quality](http://www.keysight.com/quality)  
Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2008  
Quality Management System

**Keysight Channel Partners**  
[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)  
Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

[www.keysight.com/find/connectivity](http://www.keysight.com/find/connectivity)

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

**Americas**

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

**Asia Pacific**

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

**Europe & Middle East**

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
(BP-07-01-14)

