



Agilent E6568B W-CDMA/GSM/GPRS Wireless Test Manager

Product Overview

Powerful, easy-to-use test automation software for design and manufacturing helps you get multi-format GSM/GPRS and W-CDMA wireless devices released and into volume production fast

Test Supported

W-CDMA call processing

- Mobile registration
- Base station (BS) originated call
- Mobile station origination
- BS release
- Hard handoff (channel)
- W-CDMA to GSM handoff

W-CDMA transmitter tests

- Maximum output power
- Frequency error
- Minimum output power
- Occupied bandwidth (OBW)
- Spectrum emission mask (SEM)
- Adjacent channel leakage power ratio (ACLR)
- Error vector magnitude (EVM)
- PRACH Tx On/Off power
- Inner loop power control
- Open loop power control

W-CDMA receiver tests

- BER

GSM/GPRS call processing

- GSM page (base station) origination
- GSM MS (mobile station) origination
- GSM end call (base station release)
- GPRS Start/End connection
- GPRS ETSI A, ETSI B, and Agilent BLER test modes
- PGSM, EGSM, DCS, PCS, RGSM, 450 MHz, 480 MHz, 750 MHz, and 850 MHz bands
- Channel and band changes
- Change downlink traffic power
- GSM handover
- GPRS handover



GSM/GPRS transmitter tests

- Output RF spectrum
- Phase and frequency error
- Power versus time
- Tx power
- Power versus level (GSM only)
- Burst timing error

GSM receiver tests

- Fast BER
- BER
- Rx level and quality report

GPRS receiver tests

- BER
- BLER
- BLER report

GSM/GPRS Rx/Tx tests

- Fast general

General tests

- Current drain
- GSM/GPRS Tx current drain at level
- Voice quality



Hardware Supported

Test instruments

- Agilent 8960 Series 10 wireless communications test set
- E5515C mainframe (or equivalent E5515B/T) with Options 002 and 003
- Any combination of test applications
 - E1963A W-CDMA mobile test application (revision A.03 or later)
 - E1985B GSM/GPRS_AMPS/136_W-CDMA fast switching (revision A.03 or later)
 - E1968A GSM/GPRS mobile test application (revision A.01 or later), also compatible with any combination of lab applications
 - E6703A W-CDMA lab application
 - E6701C GSM/GPRS lab application
 - E6785A GSM/GPRS_W-CDMA lab application
- Agilent 66311B, 66319Bv, and 66321 power supplies
- Agilent 34970 with 34901A, 34903A, and 34907A data acquisition/switch unit

Fixtures

- Agilent E8421A wireless test fixture
- Tescom TC 5941 and TC 5942

Adapters

- Agilent 82357A USB/GPIB interface
- National Instruments GP-IB-USB-A USB to GP-IB

PC cards

- Agilent GPIB
- National Instruments GPIB
- Advantech PCI 1750 digital I/O
- Pocket 9870-3 multi-port serial

Peripherals

- Symbol LS-12220-1200A fixed bar code reader
- Symbol LS-3603MS-1200A handheld bar code reader
- HP printers
- Epson MT-U200D strip printer

PC requirements

- Microsoft® Windows XP® Professional, 2000®, NT® 4.0 or 98 Second Edition
- Microsoft Visual Basic® 6.0, Service Pack 5¹
- Microsoft Internet Explorer® Version 5.0 or later
- 500 MHz Pentium® III or higher
- 256 MB RAM recommended, 128 MB RAM minimum
- 200 MB free hard drive space
- CD-ROM
- GPIB card or converter with VISA drivers (one per test system)
- Parallel port for security key (IEEE 1284, IETF 1287)
- Serial ports for fixtures, device control, and bar code reader
- Compatible with E6571A Wireless Test Manager Run-Time License

For More Information

E6568B wireless test manager product literature is available at

www.agilent.com/find/E6568B

A demonstration and information on other wireless test manager products are available at

www.agilent.com/find/wtmanagers

8960 test set specifications, product literature, application notes, and configuration guide are available at

www.agilent.com/find/8960



Agilent Email Updates

www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.

By internet, phone, or fax, get assistance with all your test & measurement needs

Online Assistance:

www.agilent.com/find/assist

Phone or Fax

United States:

(tel) 800 452 4844

Korea:

(tel) (82 2) 2004 5004
(fax) (82 2) 2004 5115

Canada:

(tel) 877 894 4414
(fax) 905 282 6495

Latin America:

(tel) (305) 269 7500
(fax) (305) 269 7599

China:

(tel) 800 810 0189
(fax) 800 820 2816

Taiwan:

(tel) 0800 047 866
(fax) 0800 286 331

Europe:

(tel) (31 20) 547 2323
(fax) (31 20) 547 2390

Other Asia Pacific Countries:

(tel) (65) 6375 8100
(fax) (65) 6836 0252

Email: tm_asia@agilent.com

Japan:

(tel) (81) 426 56 7832
(fax) (81) 426 56 7840

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2003

Printed in USA, December 4, 2003

5989-0406EN

1. Not required to run software, required for Visual Basic test development capability

Microsoft Windows XP Professional, 2000, NT, Visual Basic, and Internet Explorer are U.S. registered trademarks of Microsoft Corporation.

Pentium is a registered trademark of Intel Corporation.

