

Keysight E1735A USB Axis Module

Data Sheet



The Keysight Technologies, Inc. E1735A USB Axis Module is the electronic interface for the 5519A/B laser head used in the Keysight 5530 Laser Calibration System. The axis module also provides the interface for both the optional remote control unit and optional A-quad-B encoder input. The axis module communicates via a standard high-speed USB interface with the system PC running Microsoft Windows operating system (Windows 98 or later).

Specifications

Measurement range	
Linear interferometer	0 - 84 m (± 42 m)
Typical resolution	
Linear interferometer	1 nm
Plane mirror interferometer	0.5 nm
Angular interferometer	0.006 arc sec
Measurement frequency	
	100 kHz - 10 MHz
Data sampling rate	
	100 kHz
A-quad-B input rate	
	> 2 ns edge-to-edge, or < 10 MHz
Power requirement	
	+5 V, 280 mA maximum current (typical)
Operating temperature	
	0 - 40 °C (32 - 104 °F)
Dimensions	
	102 x 63 x 24 mm (4.02 x 2.48 x 0.95 in)
Weight	
	200 g (0.44 lb)

Related Literature

Publication title	Publication number
Keysight 5530 Laser Calibration System Brochure	5989-9354EN
Keysight 5530 Laser Calibration System Data Sheet	5989-9712EN

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/5530

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-05-19-14)