

# Keysight Technologies 55290B Rotary Axis Measurement Kit

## Data Sheet



To make angular position measurements the following products are required:

- Basic 5530 Laser Calibration System
- Angular Optics Kit (55281A)
- Rotary Axis Measurement Kit (55290B)
- Fixturing Kit (55290A-744)
- Metrology Application Software (10747F rev F.04.04 or later)

### Specifications when used with the Angular Optics Kit (55281A)

Accuracy	$\pm 1.0$ arc sec
Repeatability	$\pm 0.8$ arc sec
Resolution	0.36 arc sec
Max rpm	30 rpm
Mounting orientation	Random (includes upside down)
Operating temperature	0 – 40 °C (32 – 104 °F)
Dimensions in storage case	560 x 455 x 265 mm (22.06 x 17.93 x 10.44 in)



Ship weight in storage case


26.4 kg (58 lb)

## Components of the 55290B Rotary Axis Measurement Kit

Description	Qty
1 Socket-head cap screw, M6 x 12 mm	4
2 Hex-allen key ball point, 5 mm	1
3 Hex-key ball end, 2.5 mm	1
4 Storage case	1
5 Signal interpolator	1
6 Shaft, 200 mm	1
7 Shaft, 300 mm	1
8 Set rotation prevention	1
9 Magnetic stand	1
10 Rotary transducer head	1
11 Magnetic alignment reflector	1
12 Adapter plate	1
13 Flanged adaptor shaft	1
14 A quad B cable	1

## Related Literature

Publication title	Publication number
Keysight 5530 Laser Calibration System Brochure	5989-9354EN
Keysight 5530 Laser Calibration System Data Sheet	5989-9712EN
Keysight 55290B Rotary Axis Measurement Kit Supplemental Guide	55290-90006



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada (877) 894 4414  
 Brazil 55 11 3351 7010  
 Mexico 001 800 254 2440  
 United States (800) 829 4444

### Asia Pacific

Australia 1 800 629 485  
 China 800 810 0189  
 Hong Kong 800 938 693  
 India 1 800 112 929  
 Japan 0120 (421) 345  
 Korea 080 769 0800  
 Malaysia 1 800 888 848  
 Singapore 1 800 375 8100  
 Taiwan 0800 047 866  
 Other AP Countries (65) 6375 8100

### Europe & Middle East

Austria 0800 001122  
 Belgium 0800 58580  
 Finland 0800 523252  
 France 0805 980333  
 Germany 0800 6270999  
 Ireland 1800 832700  
 Israel 1 809 343051  
 Italy 800 599100  
 Luxembourg +32 800 58580  
 Netherlands 0800 0233200  
 Russia 8800 5009286  
 Spain 0800 000154  
 Sweden 0200 882255  
 Switzerland 0800 805353  
 Opt. 1 (DE)  
 Opt. 2 (FR)  
 Opt. 3 (IT)  
 United Kingdom 0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
 (BP-07-10-14)

[www.keysight.com/find/5530](http://www.keysight.com/find/5530)