



Agilent E4466B 1.1 m Tie Kit

Data Sheet

Connect two or more racks together

Tie kits are used to join two or more racks together to create a multi-bay configuration. The tie kit bolts the columns of adjacent racks together and completes the multi-bay solution with a cosmetic finish.

Features

- Attractive quartz gray color
- All mounting hardware included

Specifications

- Material: Cold-rolled steel
- Weight: 14 lbs (6.35 kg)
- Color: Quartz gray
- Length: 845 mm (3.27 in)
- Width: 109 mm (4.29 in)

Installation

Remove items from the cabinet that could interfere with the installation of the tie kit.

Remove side panels that will not be needed when the two cabinets are tied together. Position the two cabinets next to each other.

Put the L-shaped tie-top panel and front panel in place between the two cabinets. Secure with included mounting hardware.

Tools required for installation:

- Torx T25 screwdriver
- Socket wrenches
- Level

What you get in the box

- 1 Rear tie
- 1 Front tie
- 1 Top tie
- All mounting hardware
- Installation instructions

What changed

- Color changed from parchment white to quartz gray

Compatibility

The E4466B can be used with:

- E3660B – Agilent 1.1 m rack

Related Products

Other tie kit sizes are available.

- E4467B – Agilent 1.3 m tie kit
- E4468B – Agilent 1.6 m tie kit
- E7792A – Agilent 2.0 m tie kit

Warranty

Three year replacement



Agilent Technologies

Agilent Technologies' Test and Measurement Support, Services, and Assistance

Agilent Technologies aims to maximize the value you receive, while minimizing your risk and problems. We strive to ensure that you get the test and measurement capabilities you paid for and obtain the support you need. Our extensive support resources and services can help you choose the right Agilent products for your applications and apply them successfully. Every instrument and system we sell has a global warranty. Support is available for at least five years beyond the production life of the product. Two concepts underlie Agilent's overall support policy: "Our Promise" and "Your Advantage."

Our Promise

Our Promise means your Agilent test and measurement equipment will meet its advertised performance and functionality. When you are choosing new equipment, we will help you with product information, including realistic performance specifications and practical recommendations from experienced test engineers. When you use Agilent equipment, we can verify that it works properly, help with product operation, and provide basic measurement assistance for the use of specified capabilities, at no extra cost upon request. Many self-help tools are available.

Your Advantage

Your Advantage means that Agilent offers a wide range of additional expert test and measurement services, which you can purchase according to your unique technical and business needs. Solve problems efficiently and gain a competitive edge by contracting with us for calibration, extra-cost upgrades, out-of-warranty repairs, and on-site education and training, as well as design, system integration, project management, and other professional engineering services. Experienced Agilent engineers and technicians worldwide can help you maximize your productivity, optimize the return on investment of your Agilent instruments and systems, and obtain dependable measurement accuracy for the life of those products.

Refer to the Enclosures website for additional product information:

<http://enclosures.agilent.com>

For the latest information on Agilent's dc electronic loads, visit our web site at:
www.agilent.com/find/loads

By internet, phone, or fax, get assistance with all your test & measurement needs

Online assistance:
www.agilent.com/find/assist

Phone or Fax

United States:

(tel) 1 800 452 4844

Canada:

(tel) 1 877 894 4414

(fax) (905) 282-6495

China:

(tel) 800-810-0189

(fax) 1-0800-650-0121

Europe:

(tel) (31 20) 547 2323

(fax) (31 20) 547 2390

Japan:

(tel) (81) 426 56 7832

(fax) (81) 426 56 7840

Korea:

(tel) (82-2) 2004-5004

(fax) (82-2) 2004-5115

Latin America:

(tel) (305) 269 7500

(fax) (305) 269 7599

Taiwan:

(tel) 080-004-7866

(fax) (886-2) 2545-6723

Other Asia Pacific Countries:

(tel) (65) 375-8100

(fax) (65) 836-0252

Email: tm_asia@agilent.com

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2001
Printed in USA December 16, 2001
5988-4725EN



Agilent Technologies