

Keysight Technologies

RF & Microwave Test Accessories

75-Ohm Test Accessories

Choose high-quality for every connection

The Keysight Technologies, Inc. test accessories eliminate the weak links in your measurement system

- Guaranteed accurate and repeatable results
- Reduces cost of test

Maximize production throughput of cable TV multiport devices with the Keysight offering of 75-ohm test accessories.

These test accessories offer high accuracy and high RF performance that will maximize your production throughput at an affordable price, with operating frequency up to 12 GHz. They are ideal for testing 75-ohm devices such as taps, splitters, and amplifiers.

Ordering Information

Part number	Description
11852B	Minimum loss attenuator pad
11852B Option 004	50 ohm male to 75 ohm female
11852B Option H12	Minimum loss attenuator tested to 12 GHz
86207A	75 ohm RF bridge 300 kHz to 3 GHz
86211A	Adapter Kit, type-N and type-F, 75 ohm, DC to 2 GHz
86213A	Attenuators, 75 ohm fixed type-N
8762F	Coaxial SPDT switch, DC to 4 GHz; 75 ohm
8765F	Coaxial, SPDT, 75 ohm, DC to 4 GHz, SMB connectors
11857F	Type-F test port cable set (75 ohm)
85036B Option H12	75 ohm type N calibration kit (characterized and verified to 12 GHz)
85036E Option H06	75 ohm type N economy calibration kit (6 GHz custom cal constants disk, 8753 format)
85039B	Economy mechanical calibration kit, DC to 3 GHz, type F, 75 ohm

Note: Specials offered are subject to change without notice.

Related Literature

- 5964-3704E Keysight 8762F Coaxial Switch 75 ohm, Datasheet
 5091-2679E Keysight 8765F Coaxial Switch 75 ohm, Datasheet




Keysight 75-ohm test accessories

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/mta



This information is subject to change without notice.

© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-7647EN
www.keysight.com