Keysight Technologies Balanced Circuit Measurement with an Impedance Analyzer/LCR Meter/ Network Analyzer

Application Note





## Introduction

### How a balanced circuit differs from an unbalanced circuit

A balanced circuit has its electrical midpoint grounded. An unbalanced circuit, however, has one side grounded. A balanced circuit is typically used in communications equipment because a balanced circuit has the advantage of better spurious noise suppression.

Figure 1 shows a balanced cable which is an example of a balanced circuit. The voltages of the cable's two conductors are at every point equal in amplitude and opposite in phase. Figure 2 shows an unbalanced cable which is an example of an unbalanced circuit. Most measurement circuits in the Keysight Technologies, Inc. impedance analyzers and LCR meters are unbalanced.

### Measuring a balanced circuit with an unbalanced measurement instrument

A balanced circuit cannot be directly measured with an unbalanced measurement instrument because of the difference in their configuration.

When measuring balanced circuits, the unbalanced measuring instrument requires a Balun (balanced to unbalanced) transformer. A Balun is a type of impedance-matching RF transformer.

Figure 3 shows the configuration for measuring a balanced circuit with an unbalanced instrument.

**Note:** In balanced cable measurements, residual current in the Balun or the measuring instrument can cause measurement errors. To reduce the degree of error, perform open/short and load compensation at the measurement terminals of the Balun.

### Selecting a Balun

There are several types and brands of Balun transformers. When selecting a Balun, ensure that frequency is compatible with your measurement requirements. When you measure the impedance parameters of a balanced circuit, you don't have to use the Balun which has the same impedance with the circuit under test. However, when you measure the transmission or reflection of it, you have to use a Balun which has the same impedance with the circuit under test to keep impedance matching. Table 1 shows recommended Balun transformers.



Figure 3. Balanced cable measurement configuration

Figure 2. Unbalanced cable

٥v

### Measurement Configuration with a Balun and Compensation

### Impedance measurement configuration with Keysight 4294A impedance analyzer

Figure 4 shows impedance measurement configuration (1)/(2) with the 4294A.

### To calibrate/compensate for (1):

1. Perform open, short, and load compensation at the balanced terminals of the 16314-60011. Use the furnished compensation standards of the 16314-60011.

Standards	0Ω	PN 04191-85300
	0S	PN 04191-85302
	50 Ω	PN 04191-85301

Keysight 4294A

**c p** 

0

### To calibrate/compensate for (2):

1. Assemble a female BNC connector as shown in Figure 5.

3. Remove the connector and connect the DUT. Measure the DUT.

### Impedance measurement configuration with the Keysight 4395A(#010)

Figure 6 shows impedance measurement configuration (2) with the 4395A.

### Table 1. Recommended Balun transformers

### To calibrate/compensate:

Refer to "To calibrate/compensate for (2)" of impedance measurement configuration with 4294A impedance analyzer.

# Transmission measurement configuration with a network analyzer

Figure 7 shows transmission measurement configuration (3) with a network analyzer.

### To calibrate/compensate:

Short the terminals closest to the DUT to the signal out and to the test port, then perform response/thru calibration.

0	DNI 04101 00000	14010 111000011					
5	PN 04191-85302	Unb/Bal. (W)	Bandwidth	Type No.	Suppliers		
0 Ω PN 04191-853	PIN 04191-85301	50:50	100 Hz to 10 MHz	16315-60011	Keysight		
		50:100	100 Hz to 10 MHz	16316A	Keysight		
		50:600	100 Hz to 3 MHz	16317A	Keysight		
		50:50	0.1–125 MHz	0001BB	North Hills Signal Processing		
		50:75	0.1–125 MHz	0101BB	North Hills Signal Processing		
		50:100	0.1–125 MHz	0300BB	North Hills Signal Processing		
		50:600	0.1–65 MHz	0700BB	North Hills Signal Processing		
	$\sim$	75:50	0.1–100 MHz	1000BB	North Hills Signal Processing		
	$\bigcirc$	75:75	0.1–100 MHz	1100BB	North Hills Signal Processing		
		75:100	0.1–100 MHz	1300BB	North Hills Signal Processing		
lp l	Hc	75:600	0.1–60 MHz	1700BB	North Hills Signal Processing		
0							





Figure 7. Measurement configuration (3)

### Appendix: Balun Transformer Information

Balun transformers are excellent interfaces for measuring balanced components or circuits. They can be used with unbalanced system measurement instruments such as impedance analyzers, LCR meters, and/or network analyzers (that are unbalanced system measurement instruments).



Figure 8. 16314-60011 and 16315-60011

### 16314-60011

The 16314-60011 can be directly connected to a 4-terminal-pair impedance analyzer or an LCR meter. High-accuracy impedance measurements of balanced devices can be made by using the OPEN/SHORT/LOAD characteristic. This unique feature of the Keysight impedance analyzer and LCR meters is performed at the binding posts by using the furnished shorting plate and a 50  $\Omega$  load resistor.

- Wide frequency range (100 Hz to 10 MHz) is covered.
- Recommended instruments:
  - 4294A precision impedance analyzer
  - 4284A precision LCR meter
  - 4285A precision LCR meter
  - E4980A precision LCR meter

### 16315-60011, 16316A, 16317A

- Reflection and transmission measurements of balanced devices and circuits can be measured with a network analyzer.
- With the furnished load resistor (50 Ω, 100 Ω, 600 Ω) and short plate, calibration can be performed for high-accuracy measurements.
- Depending on the impedance of the device, balanced impedance of 50 Ω, 100 Ω, or 600 Ω can be selected.
- Wide frequency range (100 Hz to 10 MHz (Keysight 16317A covers up to 3 MHz))
- Recommended instruments:
  - 4395A 500 MHz network/ spectrum/impedance analyzer
  - 4396B 1.8 GHz network/ spectrum/impedance analyzer
  - 4294A precision impedance analyzer

### Specifications

Specifications describe the instrument's warranted performance over the temperature range of 0 to 50 °C (except where noted) and after 30-minute warm-up time.

### Table 2. Balun transformers specifications

Item		16314-60011	16315-60011	16316A	16317A
Terminal configuration & Bal nominal characteristic Un impedance poi	Balanced port	Binding posts 2 signal terminals and 1 ground terminal (signal terminal spacing: 14.0 mm)			
		50Ω	50Ω	100Ω	600Ω
	Unbalanced	4 BNC connectors 1 BNC connector			
	port	50Ω			
Size (mm)		89(W) x 56(H) x 133 (D)	89(W) × 55(H) × 121 (D)		
Weight (g)		400 350			
Operating temperature		0 to 55 °C			
Operating humidity		≤ 95% RH (@ 40 °C)			
Non-operation tempe	erature	-40 to +70 °C			
Non-operating humidity ≤ 90% RH (@ 65 °C)					
Furnished accessories		50Ω load resistor	$50\Omega$ load resistor	100 $\Omega$ load resistor	$600\Omega$ load resistor
		Shorting plate	Shorting plate	Shorting plate	Shorting plate
		Manual	Manual	Manual	Manual

### Supplemental Characteristics

Supplemental characteristics are intended to provide information useful in applying the instrument by giving non-warranted performance parameters.

Table 3. Balun transformers supplementa	l characteristics	(at 23 ± 5	°C)
---	-------------------	------------	-----

Item	16314-60011	16315-60011	16316A	16317A
Operating frequency	100 Hz to 10 MHz			100 Hz to 3 MHz
Insertion loss	≤ 1.0 dB (¢			@100 kHz)
Freq. response	$\leq$ 1.0 dB (relative to the insertion loss at 100 kHz)		Sertion loss at $\leq \pm 1.5$ dB (relative to the insertion loss at 100 kHz)	
Return loss	$\leq$ 10 dB (100 Hz Freq. < 300 Hz)			≤ 10 dB (100 Hz Freq. < 300 MHz)
	≤ 20 dB (300 Hz Freq. < 7 MHz)			≤ 20 dB (300 MHz Freq. 1 MHz)
	$\leq$ 17 dB (7 MHz Freq. < 10 MHz)			≤ 15 dB (1 MHz < Freq. 3MHz)
Common mode	$\leq$ 50 dB (100 Hz Freq. < 3 MHz)		1	≤ 50 dB (100 Hz Freq. < 1 MHz)
	$\leq$ 45 dB (3 MHz Freq. < 5 MHz)			≤ 45 dB (1 MHz Freq. < 3 MHz)
1035	$\leq$ 40 dB (5 MHz Freq. < 10 MHz)			

### Web Resource

www.keysight.com/find/impedance www.keysight.com/find/lcrmeters

### References

Impedance Measurement Handbook, Publication Number 5950-3000

### For information on Balun, contact the manufacturers:

North Hills Signal Processing A Porta Systems Company 575 Underhill Blvd. Syosset, NY 11791 Tel: (516) 682 7740 Fax: (516) 682 7704 www.northhills-sp.com/contact.html

#### myKeysight

myKeysight

"X10

#### www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

### www.axiestandard.org

 $\mathsf{AdvancedTCA}^{\textcircled{R}}$  Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA<sup>®</sup>, AdvancedTCA<sup>®</sup>, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.

#### www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



#### www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



### Three-Year Warranty www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



### Keysight Assurance Plans

#### www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



### www.keysight.com/quality

Keysight Technologies, Inc. DEKRA Certified ISO 9001:2008 Quality Management System

### **Keysight Channel Partners**

### www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

This document was formerly known as application note number 346-2.

www.keysight.com/find/impedance www.keysight.com/find/lcrmeters

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

#### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

#### Europe & Middle East

United Kingdom

For other unlisted countries: www.keysight.com/find/contactus (BP-07-10-14)



This information is subject to change without notice. © Keysight Technologies, 2008 - 2014 Published in USA, July 31, 2014 5091-4480E www.keysight.com