

# Keysight 33220A

## 20 MHz Function/Arbitrary Waveform Generator

### Data Sheet



LXI

### Product Discontinuance Notice

The 33220A function generator and all associated options will be discontinued December 1, 2016. The last date this product can be ordered is November 30, 2016.

- For new product purchases, Keysight recommends the 33500B Trueform Series waveform generators.
- For more information, as well as to access to detailed migration guides, please visit [www.keysight.com/find/nextgenFGs](http://www.keysight.com/find/nextgenFGs)
- To contact a product selection expert, visit [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

## Key Features

- Fully compliant to LXI Class C specification
- 20 MHz Sine and Square waveforms
- Pulse, Ramp, Triangle, Noise, and DC waveforms
- 14-bit, 50 MSa/s, 64 k-point arbitrary waveforms
- AM, FM, PM, FSK, and PWM modulation types
- Linear & logarithmic sweeps and burst operation
- 10 mV<sub>pp</sub> to 10 V<sub>pp</sub> amplitude range
- Graph mode for visual verification of signal settings
- Connect via USB, GPIB and LAN

## Uncompromising performance for functions and waveforms

The Keysight Technologies 33220A function/arbitrary waveform generator uses direct digital synthesis (DDS) techniques to create a stable, accurate output signal for clean, low distortion sine waves. It also gives you square waves with fast rise and fall times up to 20 MHz and linear ramp waves up to 200 kHz.

## Pulse generation

The 33220A can generate variable-edge-time pulses up to 5 MHz. With variable period, pulse width, and amplitude the 33220A is ideally suited to a wide variety of applications requiring a flexible pulse signal.

## Custom waveform generation

Use the 33220A to generate complex custom waveforms. With 14-bit resolution, and a sampling rate of 50 MSa/s, the 33220A gives you the flexibility to create the waveforms you need. It also lets you store up to four waveforms in nonvolatile memory.

The Keysight IntuiLink arbitrary waveform software allows you to easily create, edit, and download complex waveforms using the waveform editor. Or you can capture a waveform using IntuiLink for Oscilloscope and send it to the 33220A for output. To find out more about IntuiLink, visit [www.keysight.com/find/intuilink](http://www.keysight.com/find/intuilink).

## Easy-to-use functionality

Front-panel operation of the 33220A is straight-forward and user friendly. You can access all major functions with a single key or two. The knob or numeric keypad can be used to adjust frequency, amplitude, offset, and other parameters. You can even enter voltage values directly in V<sub>pp</sub>, V<sub>rms</sub>, dBm, or as high and low levels. Timing parameters can be entered in Hertz (Hz) or seconds.

Internal AM, FM, PM, FSK, and PWM modulation make it easy to modulate waveforms without the need for a separate modulation source. Linear and logarithmic sweeps are also built in, with sweep rates selectable from 1 ms to 500 s. Burst mode operation allows for a user-selected number of cycles per period of time. GPIB, LAN, and USB interfaces are all standard, plus you get full programmability using SCPI commands.

## External frequency reference (Option 001)

The 33220A external frequency reference lets you synchronize to an external 10 MHz clock, to another 33220A, or to a Keysight 33250A. Phase adjustments can be made from the front panel or via a computer interface, allowing precise phase calibration and adjustment.

# Measurement Characteristics

## Waveforms

Standard	Sine, Square, Ramp, Triangle, Pulse, Noise, DC
Built-in arbitrary	Exponential rise, Exponential fall, Negative ramp, Sin(x)/x, Cardiac

## Waveforms Characteristics

### Sine

Frequency Range	1 $\mu$ Hz to 20 MHz
Amplitude Flatness <sup>[1], [2]</sup> (relative to 1 kHz)	< 100 kHz 0.1 dB 100 kHz to 5 MHz 0.15 dB 5 MHz to 20 MHz 0.3 dB

### Harmonic distortion<sup>[2], [3]</sup>

	< 1 V <sub>pp</sub>	$\geq$ 1 V <sub>pp</sub>
DC to 20 kHz	-70 dBc	-70 dBc
20 kHz to 100 kHz	-65 dBc	-60 dBc
100 kHz to 1 MHz	-50 dBc	-45 dBc
1 MHz to 20 MHz	-40 dBc	-35 dBc

### Total harmonic distortion<sup>[2], [3]</sup>

DC to 20 kHz	0.04%
--------------	-------

### Spurious (non-harmonic)<sup>[2], [4]</sup>

DC to 1 MHz	-70 dBc
1 MHz to 20 MHz	-70 dBc + 6 dB/octave

### Phase noise

(10 kHz offset)	-115 dBc / Hz, typical
-----------------	------------------------

### Square

Frequency range	1 $\mu$ Hz to 20 MHz
Rise/Fall time	< 13 ns
Overshoot	< 2%
Variable duty cycle	20% to 80% (to 10 MHz) 40% to 60% (to 20 MHz)

### Asymmetry (@ 50% duty)

	1% of period + 5 ns
--	---------------------

### Jitter (RMS)

	1 ns + 100 ppm of period
--	-----------------------------

### Ramp, Triangle

Frequency range	1 $\mu$ Hz to 200 kHz
Linearity	< 0.1% of peak output
Variable Symmetry	0.0% to 100.0%

### Pulse

Frequency range	500 $\mu$ Hz to 5 MHz
Pulse width	20 ns minimum, (period $\leq$ 10s)
Variable edge time	< 13 ns to 100 ns
Overshoot	< 2%
Jitter (RMS)	300 ps + 0.1 ppm of period

## Noise

Bandwidth	9 MHz typical
<b>Arbitrary</b>	
Frequency range	1 $\mu$ Hz to 6 MHz
Waveform length	2 to 64 k points
Amplitude resolution	14 bits (including sign)
Sample rate	50 MSa/s
Min. Rise/Fall Time	35 ns typical
Linearity	< 0.1% of peak output
Settling Time	< 250 ns to 0.5% of final value
Jitter (RMS)	6 ns + 30 ppm
Non-volatile memory	four waveforms

## Common Characteristics

### Frequency

Accuracy <sup>[5]</sup>	$\pm$ (10 ppm + 3 pHz) in 90 days $\pm$ (20 ppm + 3 pHz) in 1 year
-------------------------	---

Resolution	1 $\mu$ Hz
------------	------------

### Amplitude

Range	10 mV <sub>pp</sub> to 10 V <sub>pp</sub> into 50 $\Omega$ 20 mV <sub>pp</sub> to 20 V <sub>pp</sub> into open circuit
-------	---

### Accuracy<sup>[1], [2]</sup> (at 1 kHz)

	$\pm$ 1% of setting $\pm$ 1 mV <sub>pp</sub>
--	---

Units	V <sub>pp</sub> , V <sub>rms</sub> , dBm
-------	--

Resolution	4 digits
------------	----------

### DC Offset

Range (peak AC + DC)	$\pm$ 5 V into 50 $\Omega$ $\pm$ 10 V into open circuit
----------------------	--

Accuracy <sup>[1], [2]</sup>	$\pm$ 2% of offset setting $\pm$ 0.5% of amplitude $\pm$ 2 mV
------------------------------	---

Resolution	4 digits
------------	----------

### Main Output

Impedance	50 $\Omega$ typical
Isolation	42 Vpk maximum to earth

Protection	Short-circuit protected, overload automatically disables main output
------------	--

## External Frequency Reference (Option 001)

### Rear Panel Input

Lock Range	10 MHz $\pm$ 500 Hz
Level	100 mV <sub>pp</sub> to 5 V <sub>pp</sub>
Impedance	1 k $\Omega$ typical, AC coupled
Lock Time	< 2 seconds

## Rear Panel Output

Frequency	10 MHz
Level	632 mV <sub>pp</sub> (0 dBm), typical
Impedance	50 $\Omega$ typical, AC coupled

## Phase Offset

Range	+ 360° to - 360°
Resolution	0.001°
Accuracy	20 ns

## Modulation

### AM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Depth	0.0% to 120.0%

### FM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	DC to 10 MHz

### PM

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0.0 to 360.0 degrees

### PWM

Carrier waveform	Pulse
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0% to 100% of pulse width

### FSK

Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	50% duty cycle square (2 mHz to 100 kHz)

## External Modulation Input<sup>[6]</sup> (for AM, FM, PM, PWM)

Voltage range	$\pm$ 5 V full scale
Input impedance	5 k $\Omega$ typical
Bandwidth	DC to 20 kHz

## Measurement Characteristics (Continued)

### Sweep

Waveforms	Sine, Square, Ramp, Arb
Type	Linear or Logarithmic
Direction	Up or Down
Sweep time	1 ms to 500 s
Trigger	Single, External, or Internal
Marker	falling edge of sync signal (programmable frequency)

### Burst<sup>[7]</sup>

Waveforms	Sine, Square, Ramp, Triangle, Pulse, Noise, Arb
Type	Counted (1 to 50,000 cycles), Infinite, Gated
Start/Stop Phase	-360° to +360°
Internal Period	1 μs to 500 s
Gate Source	External trigger
Trigger source	Single, External or Internal

### Trigger Characteristics

Trigger input	
Input level	TTL compatible
Slope	Rising or Falling, selectable
Pulse width	> 100 ns
Input impedance	>10 kΩ, DC coupled
Latency	< 500 ns
Jitter (rms)	6 ns (3.5 ns for pulse)
Trigger output	
Level	TTL compatible into ≥ 1 kΩ
Pulse width	> 400 ns
Output Impedance	50 Ω, typical
Maximum rate	1 MHz
Fanout	≤ 4 Keysight 33220As

### Programming Times (typical)

Configuration times			
	USB	LAN	GPIB
Function Change	111 ms	111 ms	111 ms
Frequency Change	1.5 ms	2.7 ms	1.2 ms
Amplitude Change	30 ms	30 ms	30 ms
Select User Arb	124 ms	124 ms	123 ms
Arb Download Times (binary transfer)			
	USB	LAN	GPIB
64 k points	96.9 ms	191.7 ms	336.5 ms
16 k points	24.5 ms	48.4 ms	80.7 ms
4 k points	7.3 ms	14.6 ms	19.8 ms

### General

Power Supply	CAT II 100 - 240 V @ 50/60 Hz (-5%, +10%) 100 - 120 V @ 400 Hz (±10%)
Power Consumption	50 VA max
Operating Environment	IEC 61010 Pollution Degree 2 Indoor Location
Operating Temperature	0 to 55 °C
Operating Humidity	5% to 80% RH, non-condensing
Operating Altitude	Up to 3000 meters
Storage Temperature	-30 to 70 °C
State Storage Memory	Power off state automatically saved. Four user-configurable stored states
Interface	USB, GPIB, and LAN standard
Language	SCPI - 1993, IEEE-488.2
Dimensions (W x H x D)	
Bench top	261.1 mm x 103.8 mm x 303.2mm
Rack mount	212.8mm x 88.3mm x 272.3mm
Weight	3.4 kg (7.5 lbs)
Safety Designed to	UL-1244, CSA 1010, EN61010
EMC Tested to	MIL-461C, EN55011, EN50082-1
Vibration and Shock	MIL-T-28800, Type III, Class 5
Acoustic Noise	30 dBa
Warm-up Time	1 hour

### Footnotes

1. Add 1/10th of output amplitude and offset spec per °C for operation outside the range of 18 to 28 °C
2. Autorange enabled
3. DC offset set to 0 V
4. Spurious output at low amplitude is -75 dBm typical
5. Add 1 ppm/°C average for operation outside the range of 18 to 28 °C
6. FSK uses trigger input (1 MHz maximum)
7. Sine and square waveforms above 6 MHz are allowed only with an "infinite" burst count

## Ordering Information

Keysight 33220A  
20 MHz function/arbitrary  
waveform generator

### Accessories included

Operating manual, service manual, quick reference guide, IntuiLink waveform editor software, test data, USB cable, and power cord (see language option).

### Options

Opt. 001 External timebase reference  
Opt. A6J ANSI Z540 calibration  
Opt. AB0 Taiwan: Chinese manual  
Opt. AB1 Korea: Korean manual  
Opt. AB2 China: Chinese manual  
Opt. ABA English: English manual  
Opt. ABD Germany: German manual  
Opt. ABF France: French manual  
Opt. ABJ Japan: Japanese manual

### Other Accessories

34131A Carrying case  
34161A Accessory pouch  
34190A Rackmount kit  
34191A Dual flange kit, 2U  
34194A Dual lock link kit

**myKeysight**

**myKeysight**

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.



[www.lxistandard.org](http://www.lxistandard.org)

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



**Keysight Assurance Plans**

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



[www.keysight.com/quality](http://www.keysight.com/quality)

Keysight Electronic Measurement Group

DEKRA Certified ISO 9001:2008

Quality Management System

**Keysight Channel Partners**

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

[www.keysight.com/find/33220A](http://www.keysight.com/find/33220A)

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

**Americas**

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

**Asia Pacific**

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

**Europe & Middle East**

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
 (BP-05-29-14)