Keysight Technologies E1737A Material Temperature Sensor

Data Sheet

The E1737A Material Temperature Sensor is used with the Keysight Technologies, Inc. E1736A USB Sensor Hub as part of the 5530 Laser Calibration System. The E1737A Material Temperature Sensor connects to the E1736A USB Sensor Hub via a detachable E1739A/B/C/D sensor cable. Sensor cables come in different lengths (5 m, 10 m, 15 m, 25 m), they have easy snap-on connectors so users can quickly change cable lengths as needed.

The E1737A Material Temperature Sensor monitors the temperature of an area of the machine tool being calibrated to enable the laser calibration system to automatically compensate for dimensional changes. The sensor has a magnetic base for ease of attachment.



Specifications	
Measurement range	0 – 55 °C (32 – 131 °F)
Measurement accuracy	±0.1 °C (±0.2 °F) with yearly calibration
Measurement resolution	0.004 °C (0.007 °F)
Time constant	60 s typical
Refresh rate	per 4 s (per 15 s with Metrology Application Software 10747F Rev F.04.04 or later)
Power requirement	+3.3 V at maximum current (6 mA) +3.3 V at average current (0.3 mA)
Power dissipation	1 mW typical
Dimensions	Φ42 x 17.5 mm (Φ1.65 x 0.7 in)
Weight	30 g (0.07 lb)
Certification	ISO 17025
Warranty	3 years (5 years option available)



Related Literature

Publication title	Publication number
5530 Laser Calibration System – Brochure	5989-9354EN
5530 Laser Calibration System – Data Sheet	5989-9712EN

myKeysight

myKeysight

www.keysight.com/find/mykeysight


A personalized view into the information most relevant to you.

Three-Year Warranty



www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.





www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.





Keysight Technologies, Inc. DEKRA Certified ISO 9001:2008 Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/5530

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Laropo a madio Lace	
Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-07-10-14)

