

Keysight Technologies N9344C/N9343C/N9342C Handheld Spectrum Analyzer (HSA)

Configuration Guide



Configure your Keysight N934xC* Handheld Spectrum Analyzer (HSA)

This configuration guide will help you determine which performance options, measurement application software, accessories, and services to include with your new Keysight Technologies, Inc. N9344C, N9343C and N9342C HSAs, or to add as upgrades to an existing HSA. This step-by-step process will help you configure your N9344C/N9343C/N9342C HSAs. Capabilities that are listed as standard come with the instrument at no additional charge. Tailor the performance, and service packages to meet your requirements. Ordering optional capabilities at the time of purchase provides the lowest overall cost.

For performance information, refer to the N9344C/N9343C/N9342C Handheld Spectrum Analyzer Data Sheets. See literature numbers in the Additional Resources section on page 7.

Description	Option number	Additional information
Step 1. Select maximum frequency range (frequency range not upgradable)		
Frequency range, 1 MHz to 20 GHz	N9344C	Tunable to 9 kHz
Frequency range, 1 MHz to 13.6 GHz	N9343C	Tunable to 9 kHz
Frequency range, 100 kHz to 7 GHz	N9342C	Tunable to 9 kHz
Step 2. Add a preamplifier		
Preamplifier, 1 MHz to 20 GHz	N9344C-P20	For N9344C
Preamplifier, 1 MHz to 13.6 GHz	N9343C-P13	For N9343C
Preamplifier, 100 kHz to 7 GHz	N9342C-PA7	For N9342C
Step 3. Add a tracking generator		
Tracking generator, 5 MHz to 7 GHz	N934xC-TG7	Output level -20 dBm to 0 dBm, 1 dB step
Step 4. Add a cable and antenna tester		
Cable and antenna test, 5 MHz to 7 GHz	N9342C-CA7	<ul style="list-style-type: none"> - Exclusive to the N9342C HSA. - Offers return loss, VSWR, cable loss, and distance-to-fault (DTF). - Requires the tracking generator module (Option TG7). - Requires N9311X-201 precision mechanical calibrator (3-in-1 OSL). - Recommended accessories include N9311X-585 phase stable cable type N(m) to DIN(f), N9311X-586 phase stable cable type N(m) to N(f), and N9311X-547 adapter type N(m) to DIN(f).
Step 5. Add a GPS receiver		
GPS receiver, with built-in antenna	N934xC-GPS	Provides information on longitude, latitude, and altitude. An optional external antenna N934xC-GPA can be ordered.
Step 6. Add optional measurement features		
Spectrum monitor	N934xC-SIM	Adds spectrogram view, record, playback, and audio alert. Great tool for spectrum monitoring and interference analyzing.
Channel scanner	N934xC-SCN	Allows the user to easily measure channel power of multiple channels and export data to mapping applications like Google Earth and MapInfo.
Task planner	N934xC-TPN	Reduces test setup time by 95%, delivers test automation and consistency, and makes it easy to capture test results, generate reports, and share task plans with others. Find more information at www.keysight.com/find/taskplanner .
U2000 Series USB power sensor support	N934xC-PWM	Requires the Keysight U2000 Series USB power sensor.
U2020 X-series USB peak and average power sensor support	N934xC-PWP	Requires the Keysight U2020 X-series USB peak and average power sensor.
Security features	N934xC-SEC	Low-level and non-recoverable formatting of user memory and USB/LAN port control
EMI filters and quasi-peak detector	N934xC-EMC	Provides CISPR compliant resolution bandwidth (200 Hz, 9 kHz, 120 kHz and 1 MHz) and quasi-peak detector for basic EMI precompliance test.

** Throughout this document "N934xC" refers to N9344C, N9343C, and N9342C.

Configure your Keysight N934xC Handheld Spectrum Analyzer (HSA) (continued)

Description	Option number	Additional information
Baseband input	N9342C-BB1	Exclusive to the N9342C HSA. Offers improved RF performance below 12 MHz.
AM/FM modulation analysis	N934xC-AMA	Provides modulation metrics, including carrier power, modulation rate, and AM depth/FM deviation.
ASK/FSK modulation analysis	N934xC-DMA	Provides modulation metrics, including carrier power, ASK depth/index, and FSK deviation.
Time-gated spectrum analysis	N934xC-TMG	Measures any one of several signals separated in time, or excludes periodic interfering signals.
Step 7. Add an accessory		
Spare battery	N934xC-BAT	Lithium ion, 10.8 V, 4.56 A-hr
Spare external battery charger	N934xC-BCG	
Spare AC/DC adapter	N934xC-ADP	1 output: 15 V, 5.33 A
Automotive 12 V DC adapter and charger	N934xC-1DN	Provides DC power supply and power charging
Hard transit case	N934xC-1TC	
Adaptor, 50 to 75 Ω	N934xC-TAD	Type N(m) 50 Ω to type N(f) 75 Ω
Ergonomic soft carrying case with backpack and shoulder strap	N934xC-SCC	
External GPS antenna	N934xC-GPA	SMA-M connector
Calibrator	N9311x-201	Precision mechanical calibrator, 3-in-1 OSL, DC to 7 GHz, N(m)
Antenna	N9311x-500	70 to 1000 MHz, 65 g, 180 degree tilt angle adjustable, N(m) telescopic whip antenna
Antenna	N9311x-501	700 to 2500 MHz, 70 g, 210 mm x 20 mm, omni-directional, N(m)
Antenna	N9311x-504	700 MHz to 4 GHz, 4 dBi gain, 270 g, 340 mm x 200 mm x 25 mm, logarithmic-periodic, N(m)
Antenna	N9311x-508	680 MHz to 8 GHz, 5 dBi gain, 250 g, 340 mm x 200 mm x 25 mm, logarithmic-periodic, N(m)
Antenna	N9311x-518	680 MHz to 18 GHz, 5 dBi gain, 250 g, 340 mm x 200 mm x 25 mm, logarithmic-periodic, N(m)
Bandpass filter	N9311x-550	<ul style="list-style-type: none"> - 3 dB passband 814 to 850 MHz - Rejection \geq 36 dBc at 740 MHz, \geq 36 dBc at 915 MHz - Insertion loss \leq 0.5 dB - VSWR \leq 1.5

Configure your Keysight N934xC Handheld Spectrum Analyzer (HSA) (continued)

Description	Option number	Additional information
Step 7. Add an accessory (continued)		
Bandpass filter	N9311x-551	<ul style="list-style-type: none"> - 3 dB passband 880 to 915 MHz - Rejection ≥ 35 dBc at 826 MHz, ≥ 36 dBc at 932 MHz - Insertion loss ≤ 1 dB - VSWR ≤ 1.5
Bandpass filter	N9311x-552	<ul style="list-style-type: none"> - 3 dB passband 1707.5 to 1787.5 MHz - Rejection ≥ 35 dBc at 1550 MHz, ≥ 35 dBc at 1925 MHz - Insertion loss ≤ 0.4 dB - VSWR ≤ 1.5
Bandpass filter	N9311x-553	<ul style="list-style-type: none"> - 3 dB passband 1845 to 1915 MHz - Rejection ≥ 35 dBc at 1770 MHz, ≥ 35 dBc at 1986 MHz - Insertion loss ≤ 0.6 dB - VSWR ≤ 1.5
Bandpass filter	N9311x-554	<ul style="list-style-type: none"> - 3 dB passband 1910 to 1990 MHz - Rejection ≥ 35 dBc at 1825 MHz, ≥ 35 dBc at 2070 MHz, - Insertion loss ≤ 0.6 dB - VSWR ≤ 1.5
Adapter	N9311x-540	Type-N(m) to BNC(f), DC to 2 GHz
Adapter	N9311x-541	Type-N(m) to SMA(f), DC to 12.4 GHz
Adapter	N9311x-542	Type-N(f) to 7/16 DIN(f), DC to 7.5 GHz
Adapter	N9311x-543	Type-N(f) to BNC(m), DC to 4 GHz
Adapter	N9311x-544	Type-N(f) to 7/16 DIN(m), DC to 7.5 GHz
Adapter	N9311x-545	Type-N(f) to SMA(m), DC to 12.4 GHz
Adapter	N9311x-546	Type-N(f) to Type-N(f), DC to 18 GHz
Adapter	N9311x-547	Type-N(m) to DIN(f), DC to 7.5 GHz
Cable	N9311x-580	Phase stable, 1.5 m, N(m) to N(m)
Cable	N9311x-581	Phase stable, 3 m, N(m) to N(m)
Cable	N9311x-582	1.5 m, SMA(m) to SMA(m)
Cable	N9311x-583	1.5 m, BNC(m) to BNC(m)
Cable	N9311x-585	Phase stable, 1.5 m, N(m) to DIN(f)
Cable	N9311x-586	Phase stable, 1.5 m, N(m) to N(f)
Attenuator	N9311x-560	40 dB, N(m) to N(f), 10 watts average
Attenuator	N9311x-561	40 dB, N(m) to N(f), 50 watts average
Attenuator	N9311x-562	40 dB, N(m) to N(f), 100 watts average
Step 8. Choose a warranty		
Select coverage		
3-year warranty (return to Keysight), standard	Included	
5-year warranty assurance plan (return to Keysight)	R-51B-001-5Z	Priority warranty service includes one-time coverage for an EOS/ESD failure
Step 9. Add calibration service		
Select Keysight calibration plan		
Commercial calibration certificate with test data	N934xC-UK6	Keysight provides a commercial calibration certification; only available at time of purchase; provides measurement results.
3-year calibration assurance plan (return to Keysight)	R-50C-011-3	Priority calibration service covering all calibration costs for 3 years; 15% cheaper than buying stand-alone calibrations.
5-year calibration assurance plan (return to Keysight)	R-50C-011-5	Priority calibration service covering all calibration costs for 5 years; 20% cheaper than buying stand-alone calibrations.

Instrument Upgrades

Upgrade your existing Keysight N934xC (HSA)

Keysight provides a fast upgrade process for performance options that do not require additional hardware.

1. Place an order for the upgrade with Keysight and ask to receive the option upgrade entitlement certificate through email.
2. Redeem the certificate through the Web by following the instructions on the certificate.
3. Install the license file and latest software on the N934xC.
4. Begin using the new capability.

Installation, calibration, and verification information is available at:

- For N9344C, it is www.keysight.com/find/N9344C_upgrades
- For N9343C, it is www.keysight.com/find/N9343C_upgrades
- For N9342C, it is www.keysight.com/find/N9342C_upgrades

Description	Option number	Additional information
Instrument upgrades		
Preamplifier, 1 MHz to 20 GHz	N9344CK-P20	For N9344C
Preamplifier, 1 MHz to 13.6 GHz	N9343CK-P13	For N9343C
Preamplifier, 100 kHz to 7 GHz	N9342CK-PA7	For N9342C
GPS receiver, with built-in antenna	N934xCK-GPS	Provides information on longitude, latitude, and altitude.
Spectrum monitor	N934xCK-SIM	Adds spectrogram view, record, playback and audio alert. Great tool for spectrum monitoring and interference analyzing.
Channel scanner	N934xC-SCN	Allows the user to easily measure channel power of multiple channels and export data to mapping applications like Google Earth and MapInfo.
Task planner	N934xCK-TPN	Reduces test setup time by 95%, delivers test automation and consistency, and makes it easy to capture test results, generate reports and share task plans with others. Find more information at www.keysight.com/find/taskplanner .
U2000 Series USB power sensor support	N934xCK-PWM	Requires the Keysight U2000 Series USB power sensor.
U2020 X-series USB peak and average power sensor support	N934xCK-PWP	Requires the Keysight U2020 X-series USB peak and average power sensor.
Security features	N934xCK-SEC	Low-level and non-recoverable formatting of user memory and USB/LAN port control.
AM/FM modulation analysis	N934xCK-AMA	Provides modulation metrics, including carrier power, modulation rate, and AM depth/FM deviation.
ASK/FSK modulation analysis	N934xCK-DMA	Provides modulation metrics, including carrier power, ASK depth/index, and FSK deviation.
Time-gated spectrum analysis	N934xCK-TMG	Measures any one of several signals separated in time, or excludes periodic interfering signals.
Baseband input	N9342CK-BB1	Exclusive to the N9342C HSA. Offers improved RF performance below 12 MHz. To install this option upgrade, the N9342C HSA must have the digital board with S/N starting with "N934463012". The digital board S/N can be viewed at the System menu, [Shift], [System], {System Info}, {Show System}.
EMI filters and quasi-peak detector	N934xCK-EMC	Supports basic EMI precompliance test

Instrument Upgrades (continued)

Upgrade your existing Keysight N934xC (HSA)

Description	Option number	Additional information
Instrument upgrades		
Cable and antenna test, 5 MHz to 7 GHz	N9342CK-CA7, or N9342CK-CAU	<p>Exclusive to the N9342C HSA.</p> <p>Requires the tracking generator module (Option TG7). If Option TG7 is not installed on the N9342C, please order both N9342CK-TG7 and N9342CK-CA7. Otherwise please check the TG module S/N:</p> <p>If the TG module S/N starts with "N934263004", please order N9342CK-CA7.</p> <p>If the TG module S/N starts with "N934263003", please order N9342CK-CAU.</p> <p>TG module S/N can be viewed at the System menu, [Shift], [System], {System Info}, {Show System}.</p> <p>Requires N9311X-201 precision mechanical calibrator (3-in-1 OSL).</p> <p>Recommended accessories include N9311X-585 phase stable cable type N(m) to DIN(f), N9311X-586 phase stable cable type N(m) to N(f), and N9311X-547 adapter type N(m) to DIN(f).</p>

Hardware Upgrades

Add additional accessories to your existing Keysight N934xC (HSA)

Description	Option number	Additional information
Hardware upgrades		
Tracking generator, 5 MHz to 7 GHz	N934xCK-TG7	Output level -20 to 0 dBm, 1 dBm step
Spare battery	N9910X-870	Lithium ion, 11.1 V, 4.6 A-hr
Spare external battery charger	N934xCK-BCG	
Spare AC/DC adapter	N934xCK-ADP	1 output: 15 V, 5.33 A
Automotive 12 V DC adapter and charger	N934xCK-1DN	Provides DC power supply and power charging
Hard transit case	N934xCK-1TC	
Adaptor, 50 to 75 Ω	N934xCK-TAD	Type N(m) 50 to type N(f) 75 Ω
Ergonomic soft carrying case with backpack and shoulder strap	N934xCK-SCC	
External GPS antenna	N934xCK-GPA	SMA-M connector

Other Information

Description

Connectivity (standard)

1 USB 2.0 type A port, female	N934xC behaves like a host controller, USB 2.0 compatible port.
1 USB 2.0 type-mini AB port, female	N934xC behaves like a slave device, USB 2.0 compatible port.
10 Base-T LAN interface	
HSA PC software	An easy-to-use, PC-based remote control tool for your N9344C/N9343C/N9342C handheld spectrum analyzer (HSA).

Instrument weight and dimensions

Dimensions (W x H x D)	318 mm x 207 mm x 69 mm (12.5 in x 8.15 in x 2.7 in)
Weight (with battery)	3.6 kg (7.9 lbs)

Hard transit case weight and dimensions

Dimensions (W x H x D)	560 mm x 460 mm x 270 mm
Weight (empty)	7.7 kg (16.9 lbs)

Standard shipped items

N934xC HSA
RoHS addendum
USB cable
Battery Li-Ion
Screwdriver
Help kit CD
Ear phone
AC/DC power supply
Quick start tutorial



Additional Resources


Related Keysight literature

Publication

Publication number	Publication title
5990-7199EN	Keysight N9344C Handheld Spectrum Analyzer Data Sheet
5990-7193EN	Keysight N9343C Handheld Spectrum Analyzer Data Sheet
5990-5587EN	Keysight N9342C Handheld Spectrum Analyzer Data Sheet

Evolving

Our unique combination of hardware, software, support, and people can help you reach your next breakthrough. **We are unlocking the future of technology.**



From Hewlett-Packard to Agilent to Keysight



myKeysight
myKeysight

myKeysight
www.keysight.com/find/mykeysight
A personalized view into the information most relevant to you.

Keysight Infoline
Keysight Infoline

Keysight Infoline
www.keysight.com/find/Infoline
Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

KEYSIGHT SERVICES

Keysight Services
www.keysight.com/find/services
Our deep offering in design, test, and measurement services deploys an industry-leading array of people, processes, and tools. The result? We help you implement new technologies and engineer improved processes that lower costs.



Three-Year Warranty
www.keysight.com/find/ThreeYearWarranty
Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans
www.keysight.com/find/AssurancePlans
Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners
www.keysight.com/find/channelpartners
Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/HSA
www.keysight.com/find/hsa-videos

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada (877) 894 4414
Brazil 55 11 3351 7010
Mexico 001 800 254 2440
United States (800) 829 4444

Asia Pacific

Australia 1 800 629 485
China 800 810 0189
Hong Kong 800 938 693
India 1 800 11 2626
Japan 0120 (421) 345
Korea 080 769 0800
Malaysia 1 800 888 848
Singapore 1 800 375 8100
Taiwan 0800 047 866
Other AP Countries (65) 6375 8100

Europe & Middle East

Austria 0800 001122
Belgium 0800 58580
Finland 0800 523252
France 0805 980333
Germany 0800 6270999
Ireland 1800 832700
Israel 1 809 343051
Italy 800 599100
Luxembourg +32 800 58580
Netherlands 0800 0233200
Russia 8800 5009286
Spain 800 000154
Sweden 0200 882255
Switzerland 0800 805353
Opt. 1 (DE)
Opt. 2 (FR)
Opt. 3 (IT)
United Kingdom 0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-06-08-16)



www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System