

# Keysight Technologies


## Hybrid Power Dividers

87302C 0.5 to 26.5 GHz

87303C 1 to 26.5 GHz

87304C 2 to 26.5 GHz

[Data Sheet](#)



# Introduction


## Features and Description

The Keysight Technologies, Inc. 87302C, 87303C, and 87304C power dividers are compact, hybrid microwave power dividers designed for power-splitting applications that require a minimal insertion loss and high isolation. The 87302C covers the entire 0.5 to 26.5 GHz frequency range with a maximum insertion loss of 1.9 dB. The 87303C and 87304C restrict the lower frequency limit for further improvement in the insertion loss. The 87303C covers 1 to 26.5 GHz with a maximum insertion loss of 1.6 dB and the 87304C operates from 2 to 26.5 GHz with a worst-case insertion loss of 1.4 dB. Maximum insertion loss of the 87302C, 87303C, and 87304C is in addition to 3 dB coupling loss. All units use industry standard 3.5 mm (SMA compatible) connectors for rugged trouble-free operation.

- High isolation
- Broadband to 26.5 GHz
- Low insertion loss
- Accurate amplitude and phase tracking

## Applications

These hybrid power dividers are excellent for any application where two-way power division with high isolation and low insertion loss is required. They typically exhibit an insertion loss that is 1 to 2 dB lower than an equivalent resistive power divider (see Figure 1).



\* Plus 3 dB Power division loss

Figure 1. Hybrid power divider.

# Product Specifications


Frequency range	Model	Band segment	VSWR	Insertion <sup>1</sup> loss (db)	Isolation (dB)	Amplitude tracking (dB)	Phase tracking (deg.)
0.5 to 26.5 GHz	87302C	0.5 to 18	1.45	1.5	19	0.3	6
		18 to 26.5	1.60	1.9	19	0.5	10
1.0 to 26.5 GHz	87303C	1.0 to 18	1.45	1.2	19	0.3	6
		18 to 26.5	1.60	1.6	21	0.5	10
2.0 to 26.5 GHz	87304C	2.0 to 18	1.45	1.1	19	0.3	6
		18 to 26.5	1.60	1.4	18	0.5	10

1. Insertion loss is in addition to 3 dB coupling loss

**Power rating** 10 W, CW (2:1 maximum load SWR)  
**Connectors** 3.5 mm F, (SMA compatible)  
**Weight** 170 g (6 oz) net, 340 g (12 oz) shipping

**Note:** Amplitude and phase tracking are the ratio of one output in dB or degrees, respectively.

## Dimensions




Dimensions are in millimeters and (inches).

Model	Dimensions		
	A	B	C
87302C	196.85 (7.75)	28.702 (1.13)	139.7 (5.50)
87303C	105.41 (4.15)	26.162 (1.03)	2.10 (53.34)
87304C	57.15 (2.25)	28.702 (1.13)	0.00 (0.00)

# Technical Performance Curves


87302C

Markers at 0.5 and 18 GHz



















87303C

Markers at 1 and 18 GHz



87304C


Markers at 2 and 18 GHz



## Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
(BP-9-7-17)

**DEKRA Certified**  
ISO 9001 Quality Management System

[www.keysight.com/go/quality](http://www.keysight.com/go/quality)  
Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2015  
Quality Management System

### myKeysight

#### myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.

[http://www.keysight.com/find/emt\\_product\\_registration](http://www.keysight.com/find/emt_product_registration)

Register your products to get up-to-date product information and find warranty information.

### KEYSIGHT SERVICES

Accelerate Technology Adoption.  
Lower costs.

#### Keysight Services

[www.keysight.com/find/service](http://www.keysight.com/find/service)

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



#### Keysight Assurance Plans

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.



This information is subject to change without notice.

© Keysight Technologies, 2017  
Published in USA, December 2, 2017  
5091-6190E

[www.keysight.com](http://www.keysight.com)