

Keysight Technologies

Accelerate Development
of Next Generation
802.11ac Wireless LAN
Transmitters-Overview

Application Brief


Achieve increased insight into chipsets and modules for enterprise wireless set top boxes, mobile computing, and medical devices with measurement solutions for R&D and design verification test (DVT) of 802.11ac transmitters

Abstract

Wireless video and wireless data networking are driving demand for standards, such as 802.11ac, which enable higher throughput. Design validation engineers must ensure their 802.11ac designs will perform well under the most demanding modulation schemes, including MIMO spatial multiplexing configurations.

To validate MIMO transmitter performance, a multi-channel signal analyzer can be used to demodulate the multi-stream waveforms and measure EVM and other physical layer parameters. The Keysight Technologies, Inc. PXI signal analyzer solutions enable MIMO 802.11ac R&D and test engineers to validate their designs with a mixture of measurement accuracy, fast speed, flexibility and scalability in a small form factor.

For measurements you can trust, with a modular, scalable design for easy upgradability, Keysight's PXI modular software and hardware solutions make 802.11ac validation easy.



Introduction

Increased use of wireless video and high-speed wireless data networking in homes and offices is driving higher throughput standards. Several standards emerged that address these new use models, including 802.11ac, which builds upon the high throughput (HT) capabilities of 802.11n to accommodate these new "Very High Throughput (VHT)" uses.

802.11ac operates in the 5 GHz 802.11a/n bands, and builds upon the high throughput enhancements of 802.11n with key advancements:

- Increased bandwidth (up to 160 MHz)
- Higher-order MIMO (up to 8x8)
- Multi-user MIMO (up to 4 users)
- Higher-order modulation (up to 256 QAM)

Application overview

Design validation engineers must ensure their 802.11ac designs will perform well under a variety of conditions, validating that their devices meet performance requirements even for the most challenging MIMO spatial multiplexing modes. To validate MIMO transmitter performance, a multi-channel signal analyzer can be used to demodulate the multi-stream waveforms and measure EVM and other physical layer parameters.

Design and validation of 802.11ac MIMO transmitters requires making EVM measurements of multi-channel MIMO spatial-multiplexing signals. A test solution should be able to make these measurements rapidly, and with a high degree of confidence. The higher-order modulation formats and wider bandwidths proposed in the 802.11ac standard require better EVM, and the test solution's residual EVM should be able to exceed these requirements and enable future modifications to the designs as they evolve, from single- and dual-channel 40 MHz to 3- and 4-channel 160 MHz MIMO designs.

Many test solutions today do not support the wide bandwidths or multi-channel capabilities required by 802.11ac designers. They may also lack a full-featured analysis package that includes hardware control and standards-based 802.11ac modulation quality measurements.



Figure 1. 4-channel M9391A PXIe vector signal analyzer configuration

Solution

Keysight addresses these requirements with the M9391A, a scalable PXI vector signal analyzer enabling up to 4 analysis channels in a single PXI chassis, 160 MHz bandwidth per channel, and fast transfer speeds over the PCIe backplane. Keysight's trusted 89600 VSA software is used to make standards-based 802.11ac physical layer measurements.

The M9391A PXI VSA offers the capabilities required for 802.11ac MIMO transmitter test design validation in a fast, scalable and flexible platform. Physical layer parametric measurements such as EVM and crosstalk can be measured with Keysight's 89600 VSA software using standards-based 802.11ac capability.

Solution details

802.11ac requires wide-bandwidth measurement capability of up to 160 MHz, and Keysight's M9391A PXIe vector signal analyzer can meet the challenge with bandwidth options up to 160 MHz per channel. The 14-bit ADC enables residual EVM which exceeds the 802.11ac standard's -32 dB EVM requirement, with residual EVM of -44 dB (nominal) for 80 MHz bandwidth signals.

The M9300A frequency reference drives the 10 MHz reference on the backplane of the PXI chassis. This 10 MHz reference is then used to synchronize the acquisition timing of multiple M9391A PXI VSAs. With this technique, timing synchronization of better than ± 5 ns can be achieved, allowing for unimpaired MIMO EVM measurements.

The M9391A supports input signals from 1 MHz to 6 GHz, easily covering the 802.11ac frequency bands and enables scalable deployment, with 1 to 4 channels configurable in a single 18-slot PXI chassis. Keysight's 89600 VSA software controls the M9391A PXI VSAs and provides the measurement algorithms for MIMO WLAN transmitter testing. The 89600 VSA software can be controlled programmatically via the .NET interface for fast automation required in many validation test scenarios.




Figure 2. 3-channel 802.11ac analysis using Keysight's 89600 VSA software.

Ordering information

Quantity	Model	Description
1-4	M9391A	PXIe vector signal analyzer 1 MHz – 6 GHz
1	M9300A	PXI frequency reference
Optional		
1	M9018A	PXIe 18-slot chassis
1	M9036A	PXIe embedded controller
1	89601B-200	89600 VSA software, transportable license
1	89601B-300	Hardware connectivity
1	89601B-BHJ	WLAN 802.11ac modulation analysis
1	89601B-B7Z	WLAN 802.11n modulation analysis
1	89601B-B7R	WLAN 802.11a/b/g modulation analysis

Want to know more?

- 802.11 WLAN Test
www.keysight.com/find/wlan
- Technical Overview: *Testing New-generation Wireless LAN*, publication number 5990-8856EN
- PXI RF Vector Signal Analyzer:
www.keysight.com/find/M9391A
- 89600 VSA software:
www.keysight.com/find/89600vsa

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



www.axiestandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



www.keysight.com/quality

Keysight Electronic Measurement Group

DEKRA Certified ISO 9001:2008

Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

PICMG and the PICMG logo, CompactPCI and the CompactPCI logo, AdvancedTCA and the AdvancedTCA logo are US registered trademarks of the PCI Industrial Computers Manufacturers Group. "PCIe" and "PCI EXPRESS" are registered trademarks and/or service marks of PCI-SIG.

www.keysight.com/find/modular

www.keysight.com/find/pxi-mimo

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-05-23-14)

