


Agilent E2071D

High-Speed GPIB Interface for HP-UX 10.20 Workstations

Data Sheet

- High-performance GPIB interface card
- Plug-in instrument control for UNIX workstations
- VISA and SICL support
- Easy access to test automation
- 750 KB/s maximum data rate



Agilent E2071D

Description

The Agilent E2071D GPIB Interface Card is a **complete hardware and software library package** for HP-UX workstations. It gives everything needed to quickly automate your test station. It provides a cost effective, easy to buy hardware/software combination.

The high-performance E2071D has a maximum data rate of 750 KB/s. The interface is supported by SICL and VISA for HP-UX 10.20. For other HP-UX operating system support contact your local Agilent sales office. SICL and VISA let you work with open I/O libraries that are portable, regardless of the I/O interface or computer platform.

The GPIB interface card plugs into one EISA slot in the backplane of your external controller. A GPIB cable connects the card to the command module in Slot 0 of the VXI mainframe or directly to a GPIB instrument.

Refer to the Agilent Technologies Website for instrument driver availability and downloading instructions, as well as for recent product updates, if applicable.

Product Specifications

Controller Max. Data Rate Start-up Time (ms)

Controller	Max. Data Rate (KB/s) *	Start-Up Time (ms) **
745i - E2071D (write)	750	0.3
745i - E2071D (read)	580	0.3

*Maximum data transfer rate is the speed of data movement.

**The transaction start-up time measures the overhead of starting up a transfer of data.

Interface Characteristics

Operating system:	HP-UX 10.20
Controller:	Series 700
I/O library:	SICL/VISA
Backplane:	EISA
Max. I/O speed:	750 KB/s
Buffering:	Built-in
Languages:	HP VEE, C/C++, BASIC

Ordering Information

Description	Product No.
High-Speed GPIB Interface for HP-UX 10.20	E2071D
Delete manual set	E2071D 0B0



Agilent Technologies

Innovating the HP Way

Related Literature

2000 Test System and VXI Catalog CD-ROM,
Agilent Pub. No. 5980-0308E (detailed specifications for VXI products)

2000 Test System and VXI Catalog,
Agilent Pub. No. 5980-0307E (overview of VXI products)

1998 Test System and VXI Products Data Book,
Agilent Pub. No. 5966-2812E

Online

Internet access for Agilent product information, services and support
www.agilent.com/find/tmdir

VXI product information
www.agilent.com/find/vxi

Defense Electronics Applications
www.agilent.com/find/defense_ATE

Agilent Technologies VXI Channel Partners
www.agilent.com/find/vxichanpart

Agilent Technologies' HP VEE Application Website
www.agilent.com/find/vee

Agilent Technologies Data Acquisition and Control Website
www.agilent.com/find/data_acq

Agilent Technologies Instrument Driver Downloads
www.agilent.com/find/inst_drivers

Agilent Technologies Electronics Manufacturing Test Solutions
www.agilent.com/go/manufacturing

**Get assistance with all your test and measurement needs at
www.agilent.com/find/assist
or check your local phone book for the Agilent office
near you.**

Agilent Technologies' test and measurement service/support commitment

Agilent strives to maximize the value our test and measurement products give you, while minimizing your risk and service/support problems. We work to ensure that each product is realistically described in the literature, meets its stated performance and functionality, has a clearly stated global warranty, and is supported at least five years beyond its production life. Our extensive self-help tools include many online resources (www.agilent.com).

Experienced Agilent test engineers throughout the world offer practical recommendations for product evaluation and selection. After you purchase an Agilent product, they can provide no-charge assistance with operation verification and basic measurement setups for advertised capabilities. To enhance the features, performance, and flexibility of your test and measurement products—and to help you solve application challenges—Agilent offers free or extra-cost product options and upgrades, and sell expert engineering, calibration, and other consulting services.

Phone and fax

United States:
Agilent Technologies
(tel) 1 800 452 4844

Canada:
Agilent Technologies Canada Inc.
(tel) 1 877 894 4414

Europe:
Agilent Technologies
Test & Measurement
European Marketing Organisation
(tel) (31 20) 547 2000

Japan:
Agilent Technologies Japan Ltd.
(tel) (81) 426 56 7832
(fax) (81) 426 56 7840

Latin America:
Agilent Technologies
Latin American Region Headquarters, U.S.A.
(tel) (305) 267 4245
(fax) (305) 267 4286

Australia/New Zealand:
Agilent Technologies Australia Pty Ltd.
(tel) 1 800 629 485 (Australia)
(fax) (61 3) 9272 0749
(tel) 0 800 738 378 (New Zealand)
(fax) (64 4) 802 6881

Asia Pacific:
Agilent Technologies, Hong Kong
(tel) (852) 3197-7777
(fax) (852) 2506-9284

Data Subject to Change
© Agilent Technologies 2000
Printed in the U.S.A. 04/2000
Publication No.: 5965-5518E



Agilent Technologies
Innovating the HP Way