

## Reduce Your Test System's Size

With the world's first LXI-compliant compact power meter



### › System readiness

Integrate into existing ATE systems for seamless operations with both LXI and non-LXI instruments

### › Lower-cost startup

Optimize rack space, and eliminate expensive GPIB interfaces and cardcages



### Agilent N8262A P-Series modular power meter



### › Remote problem solving

Access and control easily via standard Web browser and bundled soft front panel GUI

### › High portability


Deploy easily around the world with its small size



Agilent Technologies


## Fast, Efficient, Cost-Effective Creation of Test Systems

Every element of your test system plays a role in ensuring mission readiness. The Agilent N8262A P-Series dual-channel modular power meter offers 100 MSa/s real-time continuous sampling and 30-MHz video bandwidth. The N8262A is one more way Agilent helps you build greater assurance in system readiness, and frees you to focus where it counts most.



### Features

Lower-cost ATE system design	<ul style="list-style-type: none"> <li>1 U-high module</li> <li>Needs only a LAN cable for connection with other instruments</li> <li>No expensive shared power supplies, cardcages, or system controllers</li> </ul>
System-ready software	<ul style="list-style-type: none"> <li>Instrument page enables setup via standard Web browser</li> <li>Easy-to-use GUI emulation of P-Series power meter front panel for familiar usage</li> <li>IVI drivers enable programming with Agilent VEE, LabVIEW, C, C++, C#, Microsoft® Visual Basic® and MATLAB®</li> <li>Optional N1918A Power Analysis Manager for complex analysis, recording and playback functions, and more</li> </ul>
Code-compatibility with other power meters	<ul style="list-style-type: none"> <li>P-Series power meters: N1911A, N1912A</li> </ul>
Backward-compatibility with existing power sensors	<ul style="list-style-type: none"> <li>P-Series wideband power sensors: N1921A, N1922A</li> <li>E4410 CW power sensors</li> <li>E9300 and 8480 Series average power sensors</li> </ul>



contact us

Dial 800 829 4444 if you're in the United States. For your local contact, visit [www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)



more information

Visit [www.agilent.com/find/N8262A\\_dm](http://www.agilent.com/find/N8262A_dm) for detailed specifications, related application notes and more



view online demo

Watch N8262A's interactive product showcase from your desktop at [www.agilent.com/find/N8262A\\_demo](http://www.agilent.com/find/N8262A_demo)



### Agilent Email Updates

[www.agilent.com/find/emailupdates](http://www.agilent.com/find/emailupdates)  
Get the latest information on the products and applications you select.



### Agilent Direct

[www.agilent.com/find/agilentdirect](http://www.agilent.com/find/agilentdirect)  
Quickly choose and use your test equipment solutions with confidence.



[www.agilent.com/find/open](http://www.agilent.com/find/open)  
Agilent Open simplifies the process of connecting and programming test systems to help engineers design, validate and manufacture electronic products. Agilent offers open connectivity for a broad range of system-ready instruments, open industry software, PC-standard I/O and global support, which are combined to more easily integrate test system development.



[www.lxistandard.org](http://www.lxistandard.org)  
LXI is the LAN-based successor to GPIB, providing faster, more efficient connectivity. Agilent is a founding member of the LXI consortium

### Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to

[www.agilent.com/find/removealldoubt](http://www.agilent.com/find/removealldoubt)

### www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

#### Phone or Fax Americas

Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

#### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	81 426 56 7832
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

#### Europe

Austria	0820 87 44 11
Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700
Germany	01805 24 6333* *0.14€/minute
Ireland	1890 924 204
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
Switzerland (French)	44 (21) 8113811(Opt 2)
Switzerland (German)	0800 80 53 53 (Opt 1)
United Kingdom	44 (0) 7004 666666

Other European Countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

Revised: March 23, 2007

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2007  
Printed in USA, June 8, 2007  
5989-6946EN



Agilent Technologies