

Keysight Technologies

8960 Wireless Communications Test Set

HSPA Applications Including HSPA+, HSUPA, and HSDP

8960 HSPA Applications

For wireless device R&D:
E6703G W-CDMA/HSPA lab application

For manufacturing:
E1963A W-CDMA mobile test application,
HSPA Options 403, 405, 413, 423

HSPA RF Parametric and Functional Test Solution

Resolve phone design problems earlier


- Test beyond typical network conditions with simultaneous Tx/Rx at the highest data rates
- Perform real world stress test to functionally verify SMS, MMS, data throughput, video, inter-RAT handovers, and other services in the presence of realistic network impairments

Ensure high-quality introductions of new phones

- Test with the fastest, most complete, and stable 3GPP-compliant TS 34.121-1 Tx/Rx measurements in an integrated UMTS/HSPA manufacturing test solution

Limited development test equipment budget?

- Get the most for your money with the largest collection of RF-to-IP test tools in a one-box tester



Key Features

Network behaviors (Lab application only)

- 21 Mbps DL and 11.5 Mbps UL HSPA+, 14.4 Mbps HSDPA, 5.7 Mbps HSUPA – keep up with the latest planned HSPA deployment
- One-box simultaneous services – provides simultaneous voice and data
- HSPA+ continuous packet connectivity (CPC) – allows a much faster reactivation for temporarily inactive users of packet data
- HSDPA active CQI response – realistic network behavior by responding to UE requests for channel quality changes
- Digital audio interface and vocoders – provides real-time end-to-end audio capability and audio codec verification
- Multiple PDP contexts – supports two primary PDP contexts for simultaneous PS services active on one UE

Analysis tools (Lab application only)

- Interactive functional test software (N5970A) – powerful software to automate and simplify functional test of HSPA mobile devices
- RF to IP layer logging via WPA software – logs protocol messages to help troubleshoot protocol problems
- Data throughput monitor – sustained 21 Mbps HSPA+, 14.4 Mbps HSDPA, and 5.7 Mbps HSUPA

Handovers (Lab application only except where noted)

- UMTS inter-RAT – 2-cell handovers and cell reselection between 2G/3G systems including voice, data, or voice + data together
Note: 2-cell voice handover between 2G/3G systems available in test application
- 3G UMA – provides connectivity and handover to/from 3G/UMA with both voice and IP data

Network services (Lab and test applications)

- Video loopback – functional video call transmit/receipt with one test set
- End-to-end video, messaging – check functionality between two UEs


RF parametric (Lab and test applications)

- Test modes – Both signaling test mode using test control (TC) protocol and non-signaling test mode are available for HSPA+, HSUPA, and HSDPA; support of 21 Mbps DL and 11.5 Mbps UL HSPA+, 14.4 Mbps HSDPA, and 5.7 Mbps HSUPA
- Tx/Rx measurements – complete suite of HSPA RF measurements for testing all categories of HSPA/W-CDMA devices (HS-DSCH Categories 1-14 and E-DCH Categories 1-7) to meet 3GPP TS 34.121-1 test standards
- All bands support – support of all 3GPP frequency bands (I to XIV, XIX, XX, and XXI) gives flexibility to test devices built for any region
- Fast calibration – with the Fast Device Tune measurement
- Convergence testing – with the FM source, GPS source simulation

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)



www.keysight.com/go/quality
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2015
 Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.



Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/8960

www.keysight.com/find/hspa

