


Keysight Technologies E5515C/E Wireless Communications Test Set

Technical Overview



High performance hardware platform for the 8960 Series of mobile device design and manufacturing test solutions

The E5515C hardware platform for the 8960 wireless communications test set is the world's most trusted solution for wireless device manufacturing, and RF design and verification. The E5515E, designed for high performance, has improved high data rate hardware, multiple signaling and RF paths, and increased headroom to support today's cutting edge 3.5G technologies, such as 42 Mbps DC-HSDPA and MIMO. Combining the E5515C/E with the 8960 family of embedded software applications creates a cellular network emulator for testing mobile device RF, baseband and IP data traffic flows. Testing can be done via call processing or test mode control and provides:

- Industry's most accurate, repeatable, standards-compliant RF and baseband measurements
- Stable performance for end-to-end high speed IP data throughput testing
- Industry leading accuracy, reliability and measurement speed

Test performance specifications are documented in the software applications. Refer to www.keysight.com/find/8960 for available software applications.

The only test set with robust and accurate RF measurements, flexible network emulation and high data rate performance that allows you to achieve complete wireless device testing across the development lifecycle.

Flexible Configuration and Easy to Order

The 8960 can be configured to either the E5515C or E5515E hardware platform, depending on the application.

The E5515C platform has three hardware functionality options:

- Option 002 - Second RF source for GSM, GPRS and EGPRS technologies
- Option 003 - Flexible CDMA base station emulator for today's CDMA-based technologies such as cdma2000®, 1xEV-DO, W-CDMA, HSPA and HSPA+. Also needed for some GSM, GPRS and EGPRS features
- Option 004 - Digital bus for fading test solutions used with Keysight Technologies, Inc. N5106A PXB baseband generator and channel emulator

The E5515E platform includes a second RF source and flexible CDMA base station emulator. E5515E has one functionality option:

- Option 004 - Digital bus for fading test solutions used with the Keysight N5106A PXB baseband generator and channel emulator

The E5515C is upgradable to E5515E with the following upgrade path:

- E5515CU-80E - Hardware upgrade set for E5515C

Technical Specifications

These specifications apply to any E5515E or E5515C with serial number US40410101, GB4041010, MY46010000 or higher.

Specifications describe the test set's warranted performance and are valid for the unit's operation within the stated environmental range unless otherwise noted. All specifications are valid after a 30-minute warm-up period of continuous operation.

Supplemental characteristics are intended to provide typical, but non-warranted, performance parameters that may be useful in applying the instrument. These characteristics are shown in italics and labeled as "typical", or "supplemental." All units shipped from the factory meet these typical numbers at 25 °C ambient temperature without including measurement uncertainty.

These are general specifications that apply to an E5515C or E5515E mainframe over the 25 °C ±5 °C ambient temperature range. Specific test and lab application specifications can be found in the library on the 8960 Web site: www.keysight.com/find/8960

Remote programming	
GPIB	IEEE Standard 488.2
GPIB help	Pressing the front panel Help key and then any other key will cause the test set to display the GPIB syntax for that command at the bottom of the front panel display; pressing the Help key again exits this mode of operation
Remote front panel lockout	Allows remote user to disable the front panel display to improve GPIB measurement speed
Implemented functions	T6, TE0, L4, LE0, SH1, AH1, RL1, SR1, PP0, DC1, DT0, C0, and E2
General specifications	
Dimensions (H x W x D)	235 mm x 425 mm x 629 mm
Weight	31.8 kg
Display	26.7 cm, active matrix, color, liquid crystal
LAN (local area network) port	
LAN port (for firmware upgrades only)	RJ-45 connector, 100 Mbps
LAN 2 port (for high data throughput)	RJ-45 connector, 100 Mbps (for E5515C) or 1000 Mbps (for E5515E)
LAN 3 port (for future use)	RJ-45 connector, 1000 Mbps
Operating temperature	0 to +50 °C
Storage temperature	-20 to +70 °C
Power	88 to 135 Vac, 193 to 269 Vac, 50 to 60 Hz, typically 550 VA maximum
Calibration interval	Two years
EMC	Complies with European EMC Directive 2004/108/EC IEC/EN 61326-1 CISPR Pub 11 Group 1, class A AS/NZS CISPR 11 ICES/NMB-001 This ISM device complies with Canadian ICES-001. Cet appareil ISM est conforme a la norme NMB-001 du Canada.
Electrical safety	Complies with CAN/CSA 22.2 No. 61010-1-04, UL Std. 61010-1 (2nd Edition), and IEC 61010-1 (2nd Edition)
Radiated leakage due to RF generator	Typically < 1 µV induced in a resonant dipole antenna one inch from any surface except the underside and rear panel at set RF generator output frequency and output level of -40 dBm
Spurious leakage	Typically < 5 µV induced in a resonant dipole antenna one inch from any surface on the front half of all sides of the instrument at frequencies other than the RF generator output frequency and output level of -40 dBm with no cable connected to the rear-panel LAN port
Power consumption	Typically 400 to 450 W continuous

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

cdma2000 is a US registered certification mark of the Telecommunications Industry Association.

www.keysight.com/find/8960



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-3238EN
www.keysight.com