


Keysight Technologies

ENA-L RF Network Analyzers

E5061A 300 kHz to 1.5 GHz

E5062A 300 kHz to 3 GHz

Configuration Guide



Introduction

This configuration guide describes standard configurations, options, accessories and peripherals for the ENA-L RF network analyzers. For a complete description and technical specifications of the ENA-L RF network analyzers refer to the ENA-L Data Sheet available on our Web site: www.keysight.com/find/ena

ENA-L Ordering Guide

This guide is intended to assist you in the ordering process. Additional information and products (such as multiport test set, calibration kits and cables) are described throughout this document.

- = Choose ONE and ONLY one
- = Choose any combination

In step 2 through 9, to order options for the E5062A, replace E5061A with E5062A (e.g. E5062A-XXX)

Step 1: Choose a frequency range

- 300 kHz to 1.5 GHz, choose E5061A
- 300 kHz to 3 GHz, choose E5062A

Step 2: Choose the test set configuration

- T/R test set 50 Ω , choose Option E5061A-150
- T/R test set 75 Ω , choose Option E5061A-175
- S-parameter test set 50 Ω , with extended power range, choose Option E5061A-250
- S-parameter test set 75 Ω , with extended power range, choose Option E5061A-275

Step 3: If you chose T/R test set, would you like extended power range (-45 dBm to 10 dBm)?

- Yes, choose Option E5061A-1E1
- No

Step 4: Would you like to add fault location and structural return loss analysis?

- Yes, choose Option E5061A-100
- No

Step 5: Would you like a touch screen?

- Yes, choose Option E5061A-016
- No, choose Option E5061A-015

Step 6: Would you like any rack mount accessories?

- Rack mount kit only, choose Option E5061A-1CM
- Front handle kit only, choose Option E5061A-1CN
- Rack mount and front handle kit, choose Option E5061A-1CP

Step 7: Would you like to add any accessories?

- Add a keyboard, choose Option E5061A-810
- Add a mouse, choose Option E5061A-820

Step 8: Choose a language of manual set and specify quantity

- Add English manual set, choose Option E5061A-ABA and specify quantity
- Add Japanese manual set, choose Option E5061A-ABJ and specify quantity

Step 9: Would you like a commercial calibration certificate (ISO 17025 compliant) with test data?

- Yes, choose Option E5061A-1A7
- No

ENA-L RF Network Analyzer

The ENA-L is an integrated RF network analyzer with test set, synthesized RF source, 10.4-inch color LCD, floppy and hard disc drives. A 1-year return-to-Keysight service warranty is included with the each ENA-L network analyzer.

- **E5061A** 300 kHz to 1.5 GHz
- **E5062A** 300 kHz to 3 GHz

Options for the E5061A are listed in this section. To order options for the E5062A, replace E5061A with E5062A (e.g. E5062A-XXX)

Options

Test set options

- **Option E5061A-150** T/R test set 50 Ω
- **Option E5061A-175** T/R test set 75 Ω
- **Option E5061A-250** S-parameter test set 50 Ω with extended power range
- **Option E5061A-275** S-parameter test set 75 Ω with extended power range

Source power range option

- **Option E5061A-1E1** extended power range
Adds 40 dB step attenuator to T/R test set options to extend the source power range down to -45 dBm

Additional feature option

- **Option E5061A-100** fault location analysis
Adds fault location and structural return loss analysis capabilities.

Display options

- **Option E5061A-015** standard color LCD
Add standard 10.4-inch color LCD without touch screen capability
- **Option E5061A-016** touch screen color LCD
Adds touch screen capability to the standard 10.4-inch color LCD.

Accessories options

- **Option E5061A-1CM** rack mount kit
Adds a rack mount kit (part number 5063-9216)
- **Option E5061A-1CN** front handle kit
Adds a front handle kit (part number 5063-9229)
- **Option E5061A-1CP** rack mount and front handle kit
Adds a rack mount kit (part number 5188-4430)
- **Option E5061A-810** adds a keyboard
- **Option E5061A-820** adds a mouse

Documentation options

- **Option E5061A-ABA** add specified quantities of English manual set
- **Option E5061A-ABJ** add specified quantities of Japanese manual set

Certification options

- **Option E5061A-1A7** ISO 17025 compliant calibration
- **Option E5061A-A6J** ANSI Z540 compliant calibration

For online information about Keysight Technologies, Inc. service and support products visit:
www.keysight.com/find/tm_services

Waranty options

- **3 year** return-to Keysight warranty and service
- **5 year** return-to Keysight warranty and service

Measurement Accessories

A complete line of RF test accessories can be found at the Keysight RF and Microwave Test Accessories Web site:
www.keysight.com/find/accessories

Accessories are available in these connector types: 50 Ω Type-N, 3.5 mm, 7 mm, 7-16, 50 Ω Type-N , and Type-F. Test port cables and a calibration kit should be added for a complete measurement system.

50 Ω Accessories

Test port cables

Test port cables are used to connect the network analyzer to the device under test.

- **N6314A** 50 Ω Type-N RF cable, 300 kHz to 9 GHz
Includes one 610 mm (24 in) cable with male connectors (part number 8120-8862)
- **N6315A** 50 Ω Type-N RF cable, 300 kHz to 9 GHz
Includes one 610 mm (24 in) cable with both female and male connectors (part number 8121-0027)
- **11500E** cable, APC 3.5 mm (m), DC to 26.5 GHz
 - **Option 11500E-060** 60 cm cable, APC 3.5 mm (m)
Includes one 610 mm (24 in) with male connectors. 3.5 mm (f) to 50 Ω Type-N (m) adapters (1250-1744) are recommended to connect to the network analyzer's test ports.
- **11500F** 150 cm cable, APC 3.5 mm (m), DC to 26.5 GHz
Includes one 1520 mm (60 in) with male connectors. 3.5 mm (f) to 50 Ω Type-N (m) adapters (1250-1744) are recommended to connect to the network analyzer's test ports.

Calibration kits

Mechanical calibration kits include standards, such as opens, shorts and loads, which are measured by the network analyzer for increased measurement accuracy.

Electronic calibration (ECal) kits replace mechanical calibration standards with one solid-state calibration module that is controlled by the network analyzer to present many different impedances to the test ports. A full two-port calibration can be performed quickly with a single connection. This technique reduces operator errors and connector wear and abrasion.

Choose a calibration kit for each connector type to be used.

Economy, includes:

- open standards (male and female)
- short standards (male and female)
- fixed-termination standards (male and female)
- in-series adapters

Standard, includes the devices in the economy kit and adds:

- connector tools

For devices with 50 Ω Type-N connectors

Mechanical calibration kits

- **85032E** economy: DC to 6 GHz. Includes:
 - 00909-60009 Type-N (m) fixed load
 - 85032-60011 Type-N (m) open/short
- **85032F** economy: 30 kHz to 9 GHz. Includes:
 - 85032-60017 Type-N (m) fixed load
 - 85032-60018 Type-N (f) fixed load
 - 85032-60013 Type-N (m) open
 - 85032-60014 Type-N (f) open
 - 85032-60016 Type-N (m) short
 - 85032-60015 Type-N (f) short
- **Option 85032F-100** adds:
 - 85032-60021 Type-N (f) to Type-N (f) adapter
- **Option 85032F-200** adds:
 - 85032-60019 Type-N (m) to Type-N (m) adapter
- **Option 85032F-300** adds:
 - 85032-60020 Type-N (m) to Type-N (f) adapter
- **Option 85032F-500** adds:
 - 85054-60001 Type-N (f) to 7 mm adapter (two included)
 - 85054-60009 Type-N (m) to 7 mm adapter (two included)

Electronic calibration kits

- **85092C** RF ECal: 300 kHz to 9 GHz, 2 ports. Includes:
 - **Option 85092C-MOF** module with:
 - 85092-60008 Type-N (f) to Type-N (m) RF ECal module
 - **Option 85092C-00M** module with:
 - 85092-60009 Type-N (m) to Type-N (m) RF ECal module
 - **Option 85092C-00F** module with:
 - 85092-60010 Type-N (f) to Type-N (f) RF ECal module
 - **Option 85092C-00A** adds:
 - 85054-60037 Type-N (f) to Type-N (f) adapter
 - 85054-60038 Type-N (m) to Type-N (m) adapter
- **N4431A** RF ECal module: 300 kHz to 9 GHz, 4 ports
 - **Option N4431A-020**
Adds four Type-N (f) module port connectors
 - **Option N4431A-UK6**
Commercial calibration certification with test data

For devices with 3.5 mm or SMA connectors

Mechanical calibration kits

- **85033E** economy: 30 kHz to 9 GHz. Includes:
 - 85033-60016 3.5 mm (m) load
 - 85033-60017 3.5 mm (f) load
 - 85033-60018 3.5 mm (m) open
 - 85033-60019 3.5 mm (f) open
 - 85033-60020 3.5 mm (m) short
 - 85033-60021 3.5 mm (f) short
 - 8710-1761 torque wrench
- **Option 85033E-100** adds:
 - 85027-60005 3.5 mm (f) to 3.5 mm (f) adapter
- **Option 85033E-200** adds:
 - 85027-60007 3.5 mm (m) to 3.5 mm (m) adapter
- **Option 85033E-300** adds:
 - 85027-60006 3.5 mm (m) to 3.5 mm (f) adapter
- **Option 85033E-400** adds:
 - 1250-1744 3.5 mm (f) to 50 Ω Type- N (m) adapter
 - 1250-1743 3.5 mm (m) to 50 Ω Type- N (m) adapter
 - 1250-1745 3.5 mm (f) to 50 Ω Type- N (f) adapter
 - 1250-1750 3.5 mm (m) to 50 Ω Type- N (f) adapter
- **Option 85033E-500** adds:
 - 1250-1746 3.5 mm (m) to 7 mm adapter (two included)
 - 1250-1747 3.5 mm (f) to 7 mm adapter (two included)

Electronic calibration kits

- **85093C** RF ECal: 300 kHz to 9 GHz, 2 ports. Includes:
 - **Option 85093C-MOF** module with:
 - 85093-60008 3.5 mm (f) to 3.5 mm (m) RF ECal module
 - **Option 85093C-00M** module with:
 - 85093-60009 3.5 mm (m) to 3.5 mm (m) RF ECal module
 - **Option 85093C-00F** module with:
 - 85093-60010 3.5 mm (f) to 3.5 mm (f) RF ECal module
 - **Option 85093C-00A** adds:
 - 85052-60012 3.5 mm (f) to 3.5 mm (f) adapter
 - 85052-60014 3.5 mm (m) to 3.5 mm (m) adapter
- **N4431A** RF ECal module: 300 kHz to 9 GHz, 4 ports
 - **Option N4431A-010**
 - Adds four 3.5 mm (f) module port connectors
 - **Option N4431A-UK6**
 - Commercial calibration certification with test data

For devices with 7-16 connectors

Mechanical calibration kits

- **85038A** standard: 30 kHz to 7.5 GHz. Includes:
 - 85038-80002 7-16 (f) open
 - 85038-80003 7-16 (m) open
 - 85038-80004 7-16 (f) short
 - 85038-80005 7-16 (m) short
 - 85038-80006 7-16 (f) fixed load
 - 85038-80007 7-16 (m) fixed load
 - 8710-2175 torque wrench
 - 8710-2174 open-end wrench
- **85038F** economy: 30 kHz to 7.5 GHz. Includes:
 - 85038-80002 7-16 (f) open
 - 85038-80004 7-16 (f) short
 - 85038-80006 7-16 (f) fixed load
 - 11906-80016 7-16 (f) to 7-16 (f) adapter
- **85038M** economy: 30 kHz to 7.5 GHz. Includes:
 - 85038-80003 7-16 (m) open
 - 85038-80005 7-16 (m) short
 - 85038-80007 7-16 (m) fixed load
 - 11906-80015 7-16 (m) to 7-16 (m) adapter

Electronic calibration kits

- **85098C** RF ECal: 300 kHz to 7.5 GHz, 2 ports. Includes:
 - **Option MOF** module with:
 - 85098-60007 7-16 (m) to 7-16 (f) RF ECal module
 - **Option 00F** module with:
 - 85098-60009 7-16 (f) to 7-16 (f) RF ECal module
 - **Option 00M** module with:
 - 85098-60008 7-16 (m) to 7-16 (m) RF ECal module
 - **Option 00A** adds:
 - 11906-80015 7-16 (m) to 7-16 (m) adapter
 - 11906-80016 7-16 (f) to 7-16 (f) adapter

Adapters

- **11853A** 50 Ω Type-N accessory kit. Includes:
 - 1250-1472 Type-N (f) to Type-N (f) adapter (two included)
 - 1250-1475 Type-N (m) to Type-N (m) adapter (two included)
 - 11511A Type-N (f) short
 - 11512A Type-N (m) short
- **11878A** Type-N to 3.5 mm adapter kit. Includes:
 - 1250-1744 3.5 mm (f) to 50 Ω Type- N (m) adapter
 - 1250-1743 3.5 mm (m) to 50 Ω Type- N (m) adapter
 - 1250-1745 3.5 mm (f) to 50 Ω Type- N (f) adapter
 - 1250-1750 3.5 mm (m) to 50 Ω Type- N (f) adapter
- **11906A** 7-16 to 7-16. Includes:
 - 7-16 (m) to 7-16 (m) adapter
 - 7-16 (f) to 7-16 (f) adapter
 - 7-16 (m) to 7-16 (f) adapter (two included)
- **11906B** 7-16 to Type-N. Includes:
 - Type-N (m) to 7-16 (m) adapter
 - Type-N (f) to 7-16 (f) adapter
 - Type-N (f) to 7-16 (m) adapter
 - Type-N (m) to 7-16 (f) adapter
- **11854A** 50 Ω BNC accessory kit. Includes:
 - 1250-0929 BNC (m) short
 - 1250-1473 BNC (m) to Type-N (m) adapter (two included)
 - 1250-1474 BNC (f) to Type-N (f) adapter (two included)
 - 1250-1476 BNC (f) to Type-N (m) adapter (two included)
 - 1250-1477 BNC (m) to Type-N (f) adapter (two included)

75 Ω Accessories

Test port cables

Test port cables are used to connect the network analyzer to the device under test.

- **11857-60005** precision 75 Ω Type-N cable. Includes one 610 mm (24 in) cable with male connectors
- **11857B** precision 75 Ω Type-N cable set. Includes Type-N (m-m) and Type-N (m-f) cables
- **11857F** 75 Ω Type-N to Type-F cable set
 - **Option MOF** includes:
 - Type-N (m) to Type-F (m) cable
 - Type-N (m) to Type-F (f) cable
 - **Option OOF** includes:
 - Type-N (m) to Type-F (f) cable
 - **Option OOM** includes:
 - Type-N (m) to Type-F (m) cable

Calibration kits

Mechanical calibration kits include standards, such as opens, shorts and loads, which are measured by the network analyzer for increased measurement accuracy.

Electronic calibration (ECal) kits replace mechanical calibration standards with one solid-state calibration module that is controlled by the network analyzer to present many different impedances to the test ports. A full two-port calibration can be performed quickly with a single connection. This technique reduces operator errors and connector wear and abrasion.

Choose a calibration kit for each connector type to be used.

Economy, includes:

- open standards (male and female)
- short standards (male and female)
- fixed-termination standards (male and female)
- in-series adapters

Standard, includes the devices in the economy kit and adds:

- connector tools

For devices with 75 Ω Type-N connectors

Mechanical calibration kits

- **85036B** 300 kHz to 3 GHz, includes:
 - 00909-60019 75 Ω Type-N (m) broadband load
 - 00909-60020 75 Ω Type-N (f) broadband load
 - 85036-60012 75 Ω Type-N (m) short
 - 85036-60011 75 Ω Type-N (f) short
 - 85032-60007 75 Ω Type-N (m) open
 - 85032-20001 75 Ω Type-N (f) open body
 - 85036-60010 75 Ω Type-N (f) open center conductor extender
 - 85036-60013 75 Ω Type-N (m) to (m) adapter
 - 85036-60014 75 Ω Type-N (f) to (f) adapter
 - 85036-60015 75 Ω Type-N (m) to (f) adapter
- **85036E** 300 kHz to 3 GHz, includes:
 - 00909-60019 75 Ω Type-N (m) broadband load
 - 85036-60016 75 Ω Type N (m) combined open/short

Electronic calibration kits

- **85096C** RF ECal: 300 kHz to 3 GHz, 2 ports. Includes:
 - **Option 85096C-MOF** module with:
 - 85096-60007 Type-N (m) to Type-N (f) RF ECal module
 - **Option 85096C-OOF** module with:
 - 85096-60009 Type-N (f) to Type-N (f) RF ECal module
 - **Option 85096C-00M** module with:
 - 85096-60008 Type-N (m) to Type-N (m) RF ECal module
 - **Option 85096C-00A** adds:
 - 85036-60013 Type-N (m) to Type-N (m) adapter
 - 85036-60014 Type-N (f) to Type-N (f) adapter

For devices with 75 Ω Type-F connectors

Mechanical calibration kits

- **85039B** Standard: DC to 3 GHz, includes:
 - **Option 85039B-MOF** includes:
 - 85039-60007 Type-F (m) load
 - 85039-60008 Type-F (m) short
 - 85039-60009 Type-F (m) open
 - 85039-60004 Type-F (f) load
 - 85039-60003 Type-F (f) short
 - 85039-60005 Type-F (f) open
 - 85039-60006 Type-F (m) to Type-F (m) adapter
 - 85039-60002 Type-F (f) to Type-F (f) adapter
 - 85039-60013 Type-F (f) to Type-N (m) adapter
 - 85039-60011 Type-F (m) to Type-N (f) adapter
 - **Option 85039B-OOF** includes:
 - 85039-60004 Type-F (f) load
 - 85039-60003 Type-F (f) short
 - 85039-60005 Type-F (f) open
 - 85039-60002 Type-F (f) to Type-F (f) adapter
 - **Option 85039B-00M** includes:
 - 85039-60007 Type-F (m) load
 - 85039-60008 Type-F (m) short
 - 85039-60009 Type-F (m) open
 - 85039-60006 Type-F (m) to Type-F (m) adapter

Electronic calibration kits

- **85099C** RF ECal: 300 kHz to 3 GHz, 2 ports, includes:
 - **Option 85099C-MOF** module with:
 - 85099-60009 Type-F (m) to Type-F (f) RF ECal module
 - **Option 85099C-OOF** module with:
 - 85099-60011 Type-F (f) to Type-F (f) RF ECal module
 - **Option 85099C-00M** module with:
 - 85099-60010 Type-F (m) to Type-F (m) RF ECal module
 - **Option 85096C-00A** adds:
 - 85039-60002 Type-F (f) to Type-F (f) adapter
 - 85039-60006 Type-F (m) to Type-F (m) adapter

Adapters

- **11852B** Minimum-loss pad
 - **Option 11852B-004** Type-N connectors, 50 Ω (m) to 75 Ω (f)
 - **Option 11852B-401** Type-N connectors, 50 Ω (f) to 75 Ω (m)

General Accessories

System racks

- **5063-9229** handle kit, may be ordered as option 1CN (two included)
- **5063-9216** rack mount kit, for use without handles: may be ordered as option 1CM
- **5188-4430** rack mount kit, for use with previously supplied handles; may be ordered as option 1CP
- **E3663AC** rack mount rail kit, for use with 5063-9216 or 5188-4430

Interface cables

The following GPIB cables can be used to connect the network analyzer with an external device such as a computer

- **10833A GPIB** cable, 1.0 m (3.3 ft)
- **10833B GPIB** cable, 2.0 m (6.6 ft)
- **10833C GPIB** cable, 3.0 m (9.9 ft)
- **10833D GPIB** cable, 0.5 m (1.6 ft)

Monitors

- VGA-compatible monitor

Additional Information

ENA-L Brochure

Literature number 5989-0167EN

ENA-L Technical Specifications

Literature number 5989-0018EN

Key Web Resources

For additional ENA-L product information and literature, visit: www.keysight.com/find/ena

For electronic calibration (ECal) modules, visit: www.keysight.com/find/ecal

For Keysight RF and Microwave Test accessories, visit: www.keysight.com/find/accessories

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



www.axiestandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



www.keysight.com/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-07-10-14)