

Keysight Technologies UXG Agile Signal Generator N5193A

Configuration Guide



This configuration guide will help you determine which performance options, accessories, and services to include with your new UXG or to add as upgrades to an existing UXG.

Configure Your New UXG

This step-by-step process will help you configure your UXG agile signal generator. Tailor the performance to meet your requirements.

Included in base product

Standard options and accessories come with the UXG base model at no additional charge and do not need to be ordered. They include:

- 10 kHz frequency resolution
- 100 μ s switching speed
- Amplitude range of +10 to -10 dBm
- Standard phase noise of -117 dBc/Hz (typ) at 20 kHz offset for a 10 GHz carrier frequency
- One day of on-site startup assistance

Step 1. Select frequency range (required option; frequency range not upgradeable)

Description	Option number	Additional information
Frequency range from 10 MHz to 20 GHz	N5193A-520	Not compatible with Option 540 Includes standard adapter 3.5 mm female to 3.5 mm female
Frequency range from 10 MHz to 40 GHz	N5193A-540	Not compatible with Option 520 Includes standard adapter set, 2.4 mm female-female and 2.4 mm female - 2.9 mm female

Step 2. Choose frequency resolution

Description	Option number	Additional information
Frequency resolution 10 kHz	Standard	
Frequency resolution 0.001 Hz	N5193A-FR1	

Step 3. Choose switching speed options

Description	Option number	Additional information
Switching speed 100 μ s	Standard	List update rate 100 μ s
Switching speed 1 μ s	N5193A-SS1	List update rate 1 μ s; not compatible with Option SS4
Switching speed 180 ns	N5193A-SS4	List update rate < 180 ns; latency of 370 ns applies in fast CW mode; not compatible with Option SS1

Step 4. Choose amplitude range

Description	Option number	Additional information
Amplitude range +10 to -10 dBm	Standard	
Mechanical and solid-state attenuator	N5193A-AT2	80 dB agile range and 120 dB overall range

Step 5. Choose spectral purity options

Description	Option number	Additional information
Standard phase noise	Standard	-117 dBc/Hz (typ) at 20 kHz offset for a 10 GHz carrier frequency
Enhanced phase noise	N5193A-EP1	-126 dBc/Hz (typ) at 10 kHz offset for a 10 GHz carrier frequency

Step 6. Choose modulation options

Description	Option number	Additional information
AM, FM, phase modulation, narrowband chirp, and LF output	N5193A-UNT	Chirped pulse is settable in List mode or through SCPI commands only. FMCW chirp is settable through fast control port (FCP) in Normal mode only.
Wideband chirp (min 10%)	N5193A-WC1	Requires UNT. wideband chirp is settable in List and Streaming modes, via the FCP connector, or through SCPI commands.
Pulse modulation	N5193A-PM1	

Step 7. Choose connector configuration

Description	Option number	Additional information
Move all connectors to rear panel	N5193A-1EM	Not upgradable
Type-N (f) RF output connector	N5193A-1ED	Only available on 520 units Includes standard adapter Type-N male to 3.5 mm female
100-pin LVDS I/O interface	N5193A-CC1	Must select CC1, CC2, or CC3
50-pin BCD I/O interface	N5193A-CC2	Must select CC1, CC2, or CC3
10 GB Ethernet I/O interface	N5193A-CC3	Must select CC1, CC2, or CC3

Step 8. Choose signal creation software

Description	Option number	Additional information
Signal Studio for multi-emitter scenario generation (MESH)	N7660B	

Step 9. Choose accessory and documentation options

Description	Option number
Additional LVDS I/O interface	N5193AU-CC1
Additional BCD I/O interface	N5193AU-CC2
Additional 10 GB Ethernet I/O interface	N5193AU-CC3
Additional removable 480 GByte solid-state drive	N5193AU-SSD
Front handle kit	1CN107A
Rack mount flange kit	1CM104A
Rack mount flange kit with front handles	1CP108A
CD-ROM containing English documentation set	N5193A-CD1
100-pin LVDS cable, 1.5m length	N5193A-CA1
50-pin BCD cable, 1.5m length	N5193A-CA2
10 GB fiber optic cable, 2m length, plus two SFP+ transceivers	N5193A-CA3
Hard transit case	N5193A-AXT

Step 10. Choose calibration options

Description	Option number
Commercial calibration certificate with test data	N5193A-UK6
UXG Keysight calibration + uncertainties + guardbanding (compliant calibration)	N5193A-1A7
UXG ANSI Z540-1-1994 calibration	N5193A-A6J
Calibration assurance plan, Return-to-Keysight, 3 years	R-50C-011-3
Calibration assurance plan, Return-to-Keysight, 5 years	R-50C-011-5
Calibration assurance plan, Return-to-Keysight, 7 years	R-50C-011-7
Calibration assurance plan, Return-to-Keysight, 10 years	R-50C-011-10

Step 11. Choose startup assistance service options

Description	Option number
Remote scheduled assistance 1- 999 hours	PS-S10
Startup assistance (one-day included standard)	PS-S20-UXG
Signal generator and source basics; half-day, maximum of eight students on site	PS-T10-ASG
Custom services to be qualified by Keysight	PS-X10

Upgrade Your Existing UXG

Fast license-key upgrades for options that do not require additional hardware:

1. Place an order for the upgrade with Keysight and request to receive the software entitlement certificate through email
2. Redeem the certificate through the Web by following the instructions on the certificate
3. Install the license file using Keysight License Manager
4. Begin using the new capability

Installation, calibration, and verification information is available at:

www.keysight.com/find/UXG_upgrades

You Can Upgrade!

Options can be added after your initial purchase. Most UXG options are license-key upgradeable.




Description	Upgrade number	Requirements	Additional information
Switching speed 1 μ s	N5193AU-SS1	None	Customer installable - software, license key
Upgrade from standard speed to SS4 switching speed	N5193AU-SS4	Opt 520: all S/N's Opt 540: S/N \geq 5646xxxx	Customer installable - software, license key
Upgrade from standard speed to SS4 switching speed	N5193AU-1S4	Opt 540: S/N $<$ 5646xxxx	Return to service center, hardware, license key
Upgrade from SS1 to SS4 switching speed	N5193AU-2S4	SS1, 520: all S/N's 540: S/N \geq 5646xxxx	Customer installable - software, license key
Upgrade from SS1 to SS4 switching speed	N5193AU-3S4	SS1, 540: S/N $<$ 5646xxxx	Return to service center, hardware, license key
Upgrade from SS2 to SS4 switching speed	N5193AU-4S4	SS2, 540: S/N $<$ 5646xxxx	Return to service center, hardware, license key
Frequency resolution 0.001 Hz	N5193AU-FR1	None	Customer installable - software, license key
CD-ROM containing English documentation set	N5193A-CD1	None	
Commercial calibration certificate with test data	N5193AU-UK6	None	
AM, FM, phase modulation, narrowband chirp, and LF output	N5193AU-UNT	None	Customer installable - software, license key
Add wideband chirp (min 10%)	N5193AU-WC1	UNT	Customer-installable - software, license key
Pulse modulation	N5193AU-PM1	None	Customer installable - software, license key
Add mechanical and solid-state attenuator	N5193AU-AT2	None	Return to service center - hardware, license key
Add enhanced phase noise	N5193AU-EP1	None	Customer installable - software, license key
Add core instrument firmware enhancements	N5193AU-R2C	None	Customer installable - software, license key

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/UXG

www.keysight.com/find/EW



Unlocking Measurement Insights

This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5992-0093EN
www.keysight.com