

Keysight Technologies

PS-X10-100 Solar Cell I-V Test System


Introduction

Solar cell, technical name Photovoltaic (PV), is the booming technology which converts sunlight (Including visible or ultra violet radiation) into electricity. Due to today's growing demand for green energy, the solar cell is increasingly used in many areas, such as buildings, infrastructure and even mobile devices, as these industries become more eco-conscious. While PV devices absorb the solar irradiance and convert it into energy, the Keysight Technologies, Inc. I-V tester solution can measure the performance of various PV devices such as Silicon/ Thinfilm/ multi-junction in different power ranges. This could then be integrated with solar simulators for in-house tests. It is also suitable as a standalone for outdoor testing.




Solution

Based on Keysight N3301A based Electrical Load mainframe, this integrated solution can greatly increase the solar cell's I-V curve measure power by achieving 30A or higher efficiency and larger PV area. Further, it can apply to next generation with internal transient generator and high speed sampling digitizer which allows the sampling time to be even faster than 100 points within 10ms. With U2722A three channels 0.1nA resolution SMU, we utilize for reference cell J_s measure as solar stability monitoring during I-V measurement. As the thermal effect may contribute to any test uncertainties, additional U2355A+U2802A (Or 34970A/ 34980A as alternative) can be used as multi-channel temperature data logging for coefficient correction after post analysis. The systematic rack stack is configured as turnkey solution for measurement. The benefit of the tester itself can be separated into parts for various test needs in advance.



In addition, with Keysight VEE based platform, we provide the start up Graphical User Interface console program to provide necessary parameters.



Features

Automated test parameters include:

- P_{mpp} / V_{mpp} / I_{mpp} : Power/ Voltage/ Current maximum power point
- I_{sc} : Short circuit current
- V_{oc} : Open circuit voltage
- FF: Fill Factor
- R_s / R_{sh} : Series Resistance/ Shunt Resistance
- Luminance from Reference cell
- Multi-channel temperatures from test points

Benefits Statement

- Supply easy user interfaces to access system
- Minimizes tested connectors' attrition
- Increases test efficiency & savings on test cost
- Fast test cycle time to get result
- Easy to train operators for the I-V test

System Components

- Keysight N3301A/ N3300A DC Electronic Load Mainframe with suitable modules
- Keysight U2722A Modular Source Measure Unit
- Keysight U2355A/ U2802A 31-Channel Thermocouple Signal Conditioner or 34970A
- Keysight VEE 9.0 Console Control Platform
- On-site installation and start-up assistance services
- Operational Manual: Guideline for practical test steps to avoid tedious trial-and-error procedures

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-07-10-14)