


# Keysight Technologies

## MIMO Tx/Rx Test Solutions

### Selection Guide





## Introduction

Fourth-generation wireless communication systems like Long Term Evolution (LTE) and LTE-Advanced rely on Multiple-Input Multiple-Output (MIMO) technology to deliver on the promise of higher data rates, greater coverage areas and lower operational costs. These benefits come at the cost of more complex base stations and mobile devices, which challenge the capabilities of traditional measurement equipment and test software.

Measuring LTE MIMO operation during receiver (Rx) and transmitter (Tx) device testing requires the right combination of test instruments and techniques to evaluate the performance of LTE components and systems under real-world conditions. Keysight Technologies, Inc. offers multiple solutions to meet this need.

## Solutions for MIMO LTE Rx Test

Due to its departure from previous cellular communications networks, LTE requires fundamental changes in base station/handset design and test. Receiver testing must evaluate the receiver as a whole and test its subblocks and components to better understand their contribution to the receiver's overall performance. In cases where multiple receivers are used, each receive chain must be tested separately, prior to verifying the performance of the receivers with multiple antennas.

Keysight's solutions for MIMO LTE Rx test include the:

- N5106A PXB Multi-Channel Baseband Generator/Fader
- MXG/ESG RF signal generators
- Signal Studio software

Working together, these solutions create MIMO signals and apply real-time fading for Rx test at RF and baseband. The PXB generates MIMO signals up to 4x2 and then applies flexible real-time fading to the signals. The MXG/ESG is used as an RF upconverter (one per receive antenna). Signal Studio creates the LTE signals that are used with both the PXB and MXG/ESG hardware.

## Solutions for MIMO LTE Tx Test

MIMO Tx test in LTE-based wireless communications systems requires measurement of broadband and narrowband power, overall quality metrics (e.g., EVM), and more. Measurements are also needed to control an LTE transmitter's edge-of-band characteristics, trading off out-of-band attenuation without affecting in-channel performance. Additionally, MIMO analysis adds measurements specific to multi-channel (typically 2-4) transmitters (e.g., channel phase/timing and modulation quality), made on two or more input and output channels.

Keysight's solutions for MIMO LTE Tx test include the:

- N9010A EXA/N9020A MXA signal analyzers
- Infiniium 90000 X-Series oscilloscopes
- N7109A Multi-Channel Signal Analysis System

Keysight's 89600B Vector Signal Analysis (VSA) software runs on all three hardware platforms, providing a window into what's happening inside complex LTE-based devices. Various 89600B VSA software options are available, including: LTE-Advanced, LTE, HSPA+, Mobile WiMAX™, and 802.11n/ac.

## Which Hardware Platform is Right For You?

Dual MXAs/EXAs features:

- Up to 2 channels
- Best EVM/dynamic range
- Fully characterized RF specifications
- General-purpose application

90000 X-Series features:

- Up to 4 channels
- Widest analysis bandwidth
- General-purpose application
- Phase coherent

N7109A features:

- > 4 channels
- Extendable/scalable hardware
- Fastest measurement speed
- Phase coherent
- Pre-selected tuner, off-air measurements

## Simulation-based MIMO Solutions

SystemVue is an open simulation and modeling environment that supports MIMO investigations, as well as direct connection to test equipment for verification. For algorithm designers, SystemVue supports closed-loop Throughput and BER simulations with full coding and fading models for up to 8x8 MIMO, for LTE and LTE-Advanced, complete with antenna directivities, fading, and impairments.

For verification, SystemVue can be used to model, encode, and download MIMO test vectors for a wide variety of emerging standards, and even post-process received signals. With this capability, SystemVue can also be used to manually close feedback loops, using combinations of simulation, measurements, and one's own baseband IP, thus validating system-level performance earlier in R&D.

Keysight's solutions for simulation include:

- W1461BP SystemVue Comms Architect
- W1918EP LTE-Advanced baseband library (among other standards supported)
- W1715EP MIMO Channel Builder

## Evaluating MIMO LTE Rx/Tx Solutions

When evaluating a solution, ensure it:

- supports the basic functionality you need today and in the future (e.g., the number of channels and analysis bandwidth at a given frequency).
- has the performance required for in channel measurements (e.g., EVM).
- supports other measurements you might make, such as out-of-channel measurements.
- has enough speed to work for your manufacturing timeframe.

		R&D Life Cycle														
System Type	Technology	Technology														
		LTE-Advanced	LTE-FDD	LTE-TDD	Mobile WiMax	HSPA+	WiCon-802.11n	WiCon-802.11ac	Design	Baseband	RF	Integration	Protocol	Verification Performance		
Transmitter	Dual N9020A MXAs/N9010A EXAs	● BW Limited 25 MHz	□	□	□	□	● BW Limited 25 MHz	● BW Limited 25 MHz	□	□	□	□	□	□	●	□
	89600B VSA	□	□	□	□	□	□	□	□	□	□	□	□	□	●	□
	N7109A	□	□	□	□	□	□	● BW Limited 40 MHz	□	□	□	□	□	□	●	□
Receiver	Infinium scope	□	□	□	□	□	□	□	□	□	□	□	□	□	●	□
	SystemVue	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□
	N5106A PXB	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□
	MXGs	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□
	X-Series Signal Studio	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□
Signaling	SystemVue	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□
	E6621A PXT	□	□	□	□	□	□	□	□	□	□	□	□	□	□	□

Product has full capability  Product has general capability

## Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus) (BP-9-7-17)

**DEKRA Certified**  
ISO 9001 Quality Management System

[www.keysight.com/go/quality](http://www.keysight.com/go/quality)  
Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2015  
Quality Management System

### myKeysight

#### myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.

[http://www.keysight.com/find/emt\\_product\\_registration](http://www.keysight.com/find/emt_product_registration)

Register your products to get up-to-date product information and find warranty information.

### KEYSIGHT SERVICES

Accelerate Technology Adoption.  
Lower costs.

#### Keysight Services

[www.keysight.com/find/service](http://www.keysight.com/find/service)

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



#### Keysight Assurance Plans

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

"WiMAX," "Fixed WiMAX," "Mobile WiMAX," "WiMAX Forum," the WiMAX Forum logo, "WiMAX Forum Certified," and the WiMAX Forum Certified logo are trademarks of the WiMAX Forum. All other trademarks are the properties of their respective owners.

[www.keysight.com/find/LTE](http://www.keysight.com/find/LTE)  
[www.keysight.com/find/MIMO](http://www.keysight.com/find/MIMO)



This information is subject to change without notice.  
© Keysight Technologies, 2017  
Published in USA, December 1, 2017  
5990-7817EN  
[www.keysight.com](http://www.keysight.com)