

# High-Power Requirements for Keysight M9506A 5-Slot AXIe Chassis

In applications where the M9506A is required to support up to 1500 W of total module power, the M9506A needs to be operated at a high line voltage of 220/240 VAC.








This note describes the power requirements for the M9506A AXIe chassis in countries where the required voltage or current is not available from standard outlets. These countries include the United States, Canada, Japan, Taiwan, and Denmark. The *Keysight M9506A 5-Slot AXIe Chassis User's Guide* you receive with your chassis provides additional information on setting up and using your chassis safely.

## Power Requirements

- Input:
  - 100/120 VAC (maximum input power: 1380 W)
  - 220/240 VAC (maximum input power: 2000 W)
- ~50/60 Hz
- Well-regulated power is required.

## Outlets for 220/240 VAC

The following table shows country-specific requirements for 220/240 VAC outlets:

Country	Acceptable Outlet with Dedicated Circuit	Acceptable Outlet with Non-Dedicated Circuit
United States and Canada	 NEMA 6-15, 15A	 NEMA 6-20, 20A
Japan	 JA2-15, 15A	 JA4-20, 20A
Taiwan	 NEMA 6-15, 15A	 NEMA 6-20, 20A
Denmark	 Type K, 13A	

This information is subject to change without notice.

© Keysight Technologies 2020

March 2020

M9506-92008

[www.keysight.com](http://www.keysight.com)