


N9048B PXE EMI Receiver

Overview

This configuration guide contains information to help you configure your N9048B PXE EMI receiver to meet your requirements. Ordering optional capabilities at time of purchase provides the lowest overall cost.



Included In Base Product

Standard options and accessories come with the PXE base model at no additional charge and do not need to be ordered. They include:

- Spectrum analyzer measurement application
- EMI receiver measurement application
- Quad-core, high-performance processor, 16 GB RAM, removable solid-state drive
- High-performance digital signal processing with 2 GB capture memory
- 10 MHz analysis bandwidth
- Fast sweep capability
- Low frequency enabled
- Noise floor extension
- Front panel control for two automatic external line impedance stabilization networks (LISN)
- Enhanced display package with spectrogram, trace zoom, and zone span
- Microsoft Windows 10 operating system
- Multi-touch user interface
- User guides
- Power cord
- Front-panel protective cover

Step 1. Select maximum frequency range (required option)

Description	Option number	Additional information
Frequency range, 2 Hz to 3.6 GHz	N9048B-503	
Frequency range, 2 Hz to 8.4 GHz	N9048B-508	
Frequency range, 2 Hz to 26.5 GHz	N9048B-526	
Frequency range, 2 Hz to 44 GHz	N9048B-544	

Step 2. Add a preamplifier

Description	Option number	Additional information
Preamplifier, 100 kHz to 3.6 GHz	N9048B-P03	Compatible with frequency range option N9048B-503
Preamplifier, 100 kHz to 8.4 GHz	N9048B-P08	Compatible with frequency range option N9048B-508
Preamplifier, 100 kHz to 26.5 GHz	N9048B-P26	Compatible with frequency range option N9048B-526
Preamplifier, 100 kHz to 44 GHz	N9048B-P44	Compatible with frequency range option N9048B-544
Low noise amplifier	Standard	Standard when Option P03, P08, P26 or P44 is installed; licensed as N9048B-LNA

Step 3. Choose frequency reference

Description	Option number	Additional information
Frequency reference	Standard	Aging rate: $\pm 1 \times 10^{-6}$ /year
Precision frequency reference	N9048B-PFR	Reduces frequency drift for more accurate measurements Aging rate: $\pm 1 \times 10^{-7}$ /year

Step 4. Choose analysis bandwidth

Description	Option number	Additional information
10 MHz analysis bandwidth	Standard	
25 MHz analysis bandwidth	N9048B-B25	Extends the analysis bandwidth to 25 MHz
40 MHz analysis bandwidth	N9048B-B40	Extends the analysis bandwidth to 40 MHz

Step 5. Choose performance options

Description	Option number	Additional information
Digital processor with 2 GB capture memory	Standard	Licensed as N9048B-DP2
Fast sweep capability	Standard	Improves sweep speed at swept-tune mode; licensed as N9048B-FS1
LO/IM nulling	Standard	Minimizes the LO feed-thru and intermodulation distortion; licensed as N9048B-NUL
Noise floor extension	Standard	Improves displayed average noise level (instrument alignment based processes); licensed as N9048B-NF2
Type-N RF connector, female	N9048B-CNF	Choose Type-N RF connector for Input 1
APC 3.5 mm connector, male	N9048B-C35	Choose 3.5 mm connector for Input 1 (Input 2 remains type-N); compatible with Option 526 only
External mixing	N9048B-EXM	Provides external mixing with Keysight and third party mixers; single port for LO out and IF in (SMA female)
Wideband digital IF	N9048B-WF1	Provides wideband digital IF hardware to support Time Domain Scan capabilities; licensed as N9048B-WF1; also enables Option B25 and B40

Step 6. Add rear panel output utilities

Description	Option number	Additional information
Second IF output	N9048B-CR3	Wideband IF out; center frequency depends on IF path; output on Aux IF connector at rear panel
Y-axis screen video output	N9048B-YAS	Screen video (0-1 volt open circuit) on rear panel analog out

Step 7. Add security features

Description	Option number	Additional information
Additional removable solid-state drive (SSD)	N9048B-SS1	Provides a fully-imaged, removable SSD in addition to the one installed in instruments, with Windows 10 operating system
Exclude launch program	N9048B-SF1	Prevents the launching of Windows programs from the instrument application
Prohibit saving results	N9048B-SF2	Prevents the saving/recall of measurement results or user configurations to/from instrument's data storage

Step 8. Choose measurement application or software and license type

Note: Keysight offers 4 license types for the measurement applications and instrument features, in 2 license terms: Perpetual or Time-based.

License types:

Node-locked: Allows you to use the license on one instrument/computer at a time

Transportable: Allows you to use the license on one instrument/computer at a time. This license may be transferred to another instrument/computer using Keysight's online tool

Floating: Allows you to access the license on the networked instruments/computers from a server, one at a time. For concurrent access, multiple licenses may be purchased

USB Portable: Allows you to access the license from one instrument/computer to another by end-user only with certified USB dongle, purchased separately

License terms:

Perpetual: License can be used in perpetuity. For perpetual license holders, a separate support contract is required to access Keysight technical support and software updates

Time-based: License is time limited to a defined period, such as 12-months. A valid support contract is included in the pricing for time-based licenses.

For detailed information, we strongly recommend you visit the X-Series measurement application collection page:

www.keysight.com/find/xseriesapps

Spectrum analyzer	Standard	Traditional spectrum analysis plus many new and enhanced functions; power measurements based on industry specifications; licensed as N9060EM1E
EMI receiver	Standard	Performs EMI conducted and radiated emission measurements; licensed as N6141EM1E
Enhance display package	Standard	Includes spectrogram, trace zoom, and zone span; licensed as N90E1EDPB
Time domain scan	N9048TDSB	Provides high-overlap FFT scanning for fast signal capture and measurement; requires Option WF1
Wideband time domain scan, basic detection	N9048WT1B	Provides Accelerated Time Domain Scan with 350 MHz acquisition bandwidth and gapless Real Time Scan in 170 MHz bandwidth; requires Option WF1 and N9048TDSB
Wideband time domain scan, optimum detection	N9048WT2B	Provides Accelerated Time Domain scan with 350 MHz acquisition bandwidth and gapless Real Time Scan in 350 MHz bandwidth; requires Option WF1 and N9048TDSB
Analog demodulation	N9063EM0E	Adds one-button measurement for AM/FM/PM demodulation with metrics, tune and listen, and AF spectrum; supports audio output (output voltage proportional to frequency deviation). FM Stereo and RDS are included
SCPI command language compatibility	N9062EM0E	Adds capability to emulate the R&S ESU, ESR, and ESL EMI receivers
External source control	N90EMESCB	Controls EXG and MXG sources from the front panel of the PXE

Step 9. Choose accessories

Description	Option number	Additional information
User guide	Standard	US – English localization All user documentation is included in the PXE's embedded, context-sensitive help system and on a DVD that is shipped with the instrument User documentation can be downloaded from: www.keysight.com/find/pxe_manuals
Power cord	Standard	Dependent upon the region of use
Rack mount	1CM113A	Adds rack mount flanges to the PXE
Front handles	1CN103A	Adds front handles to the PXE
Rack mount with handles	1CP105A	Adds rack mount flanges and handles to the PXE
Rack slide	1CR014A	Adds a non-tilting rack slide to the PXE
USB DVD-ROM/CD-R/RW drive	1DVR001A	Enhances the usability of the Windows operating system
Mouse, USB interface	1MSE001A	

Step 10. Add calibration, technical training, support, and upgrade services

Description	Option number	Additional information
Commercial calibration certificate with test data	N9048B-UK6	Calibration certificate only available at time of purchase; only provides measurement results
Keysight Calibration + Uncertainties + Guardbanding (accredited calibration)	N9048B-AMG	Provides ISO 17025A accredited calibration from factory; not compatible with Option WF1
Service: 1-day start-up assistance	PS-S20-01	Training on how to operate your instrument effectively (recommended)
Calibration Assurance Plan, Return-to-Keysight, 3 years	R-50C-011-3	
Calibration Assurance Plan, Return-to-Keysight, 5 years	R-50C-011-5	
Calibration Assurance Plan, Return-to-Keysight, 7 years	R-50C-011-7	
Calibration Assurance Plan, Return-to-Keysight, 10 years	R-50C-011-10	

For more information on accessories go to:

www.keysight.com/find/accessories

Other calibration options may be available; for more information on calibration go to:

www.keysight.com/find/calibration

For more information on training and application support services go to:

www.keysight.com/find/training

Instrument Upgrades

Fast license-key upgrades for performance options that do not require additional hardware:

1. Place an order for the upgrade with Keysight and request to receive the option upgrade entitlement certificate and a one-time software upgrade license through email
2. Redeem the certificate through the Web by following the instructions on the certificate
3. Install the license file and latest software in the PXE
4. Begin using the new capability ^{1, 2}

Installation and testing information is available at: www.keysight.com/find/pxe_upgrades

Description	Upgrade number	Additional information
Upgrade to the precision frequency reference	N9048BU-PFR	
Add preamplifier, 3.6 GHz	N9048BU-P03	Not compatible with Option 508, 526 or 544; Also enables low noise amplifier
Add preamplifier, 8.4 GHz	N9048BU-P08	Not compatible with Option 503, 526 or 544; also enables low noise amplifier
Add preamplifier, 26.5 GHz	N9048BU-P26	Not compatible with Option 503, 508 or 544; also enables low noise amplifier
Add preamplifier, 44 GHz	N9048BU-P44	Not compatible with Option 503, 508 or 526; also enables low noise amplifier
Increase analysis bandwidth to 25 MHz	N9048BU-B25	
Increase analysis bandwidth to 40 MHz	N9048BU-B40	
Add second IF output	N9048BU-CR3	
Add Y-axis screen video output	N9048BU-YAS	
Add security features, exclude launch program	N9048BU-SF1	Prevents the launching of Windows programs from the instrument application
Add security features, prohibit saving results	N9048BU-SF2	Prevents the saving/recall of measurement results or user configurations to/from instrument's data storage
Add removable solid-state drive (SSD)	N9048BU-SS1	Provides additional, removable solid-state drive, with Windows 10 operating system
Add wideband digital IF	N9048BU-WF1	Provides wideband digital IF hardware to support Time Domain Scan capabilities; also enables Option B25 and B40

1. At the time of manufacture, the hardware related to many of these options was fully adjusted and the option performance was verified to be within its warranted specifications. Within one year of the initial calibration date of the analyzer, this option is fully calibrated with no further adjustment or verification testing.
2. If this analyzer has been adjusted as part of a repair or calibration during its first year, or if the analyzer is more than one year old, additional adjustment and performance verification tests are required to ensure that some newly installed options are functioning properly. However, the completion of these tests does not guarantee that the analyzer meets all warranted specifications.

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

